

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Classic pliers
Catalogue number	3623, 3627, 3621, 3622 & 3626
Date	23/02/2009

Range Description A range of general purpose pliers and cutters

Features • Hot drop forged from special alloy steel for strength and durability • Dipped PVC handles for comfort • Classic matt black/polished finish • Hardened for optimum performance • Induction hardened and precision ground cutting edges for good cutting and long life
--

 3623
 3627
 3621
 3622
 3626

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3623B 5	Classic side cutters 145mm	5013969020953	82032090	6
T3623B 6	Classic side cutters 160mm	5013969020960	82032090	6
T3627B 7	Classic heavy duty side cutters 180mm	5013969020991	82032090	6
T3621B 6	Classic combination pliers 160mm	5013969020915	82032090	6
T3621B 7	Classic combination pliers 180mm	5013969020922	82032090	6
T3621B 8	Classic combination pliers 200mm	5013969020939	82032090	6
T3622B	Snipe nose pliers 140mm	5013969020948	82032090	6
T3626B 8	Snipe nose pliers 200mm	5013969020984	82032090	6

Technical product information	Cutting capacities				
			Cutting Capacity mm diameter wire		
			Hard 2200MPa	Med/Hard 1600MPa	Soft 220MPa
	Item No	Description			
	T3623B 5	Classic side cutters 145mm	-	1.6	>3.0
	T3623B 6	Classic side cutters 160mm	-	1.6	>3.0
	T3627B 7	Classic heavy duty side cutters 180mm	-	1.8	>4.0
	T3621B 6	Classic combination pliers 160mm	1.6	2.5	>4.0
	T3621B 7	Classic combination pliers 180mm	1.6	2.5	>4.0
Standards compliance	Side cutters - DIN ISO 5749 Combination Pliers - DIN ISO 5746 Snipe Nose Pliers - DIN ISO 5745				
User health and safety information	None applicable				
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations				
Material safety data	None applicable				
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered				
Country of origin	Taiwan				

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3623B 5	47	12	145	122	50	17	220	130
T3623B 6	52	13	160	188	50	17	235	196
T3627B 7	53	14	180	270	50	17	230	278
T3621B 6	52	13	160	180	50	17	200	188
T3621B 7	53	13	180	246	50	17	235	252
T3621B 8	53	13	200	324	50	17	245	336
T3622B	50	12	145	76	50	17	185	84
T3626B 8	52	12	200	224	50	17	220	232

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3623B 5	115	250	60	860		
T3623B 6	115	250	60	1256		
T3627B 7	115	250	60	1748		
T3621B 6	115	250	60	1208		
T3621B 7	115	250	60	1592		
T3621B 8	115	250	60	2096		
T3622B	115	250	60	584		
T3626B 8	115	250	60	1472		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3623B 5	Hanger	8					80	Box
T3623B 6	Hanger	8					80	Box
T3627B 7	Hanger	8					80	Box
T3621B 6	Hanger	8					80	Box
T3621B 7	Hanger	8					80	Box
T3621B 8	Hanger	8					80	Box
T3622B	Hanger	8					80	Box
T3626B 8	Hanger	8					80	Box

