

INTERCONNECTS

SERIES 714...01X • .100" GRID ULTRA LOW PROFILE CARRIERS • SINGLE AND DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Ultra low profile receptacles sit .018" above the board
- Series 714 use MM #0552-1 and MM #0552-2 pin receptacles. See page 158 for details
- Hi-Rel, 3-finger BeCu #11 contact is rated at 3 amps. See page 251 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Single Row (.039" min. mounting hole)					
	714-XX-1-31-012000					
	Specify number of pins				01-64	
FIG. 2	Single Row (.039" min. mounting hole)					
	714-XX-1-31-018000					
	Specify number of pins				01-64	
FIG. 3	Double Row (.039" min. mounting hole)					
	714-XX-2-31-012000					
	Specify number of pins				04-64	
FIG. 4	Double Row (.039" min. mounting hole)					
	714-XX-2-31-018000					
	Specify number of pins				04-64	
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264						
SPECIFY PLATING CODE XX=						
Sleeve (Pin)		91	93	41	43	
Contact (Clip)		200 μ"Sn/Pb	200 μ"Sn/Pb	200 μ"Sn	200 μ"Sn	
		10 μ" Au	30 μ" Au	10 μ" Au	30 μ" Au	