


High Operating Temperature Poly-carbonmonofluoride Lithium Coin Batteries (BR "A" Series): Individual Specifications

BR2330A

■ Dimensions(mm)




Weight:3.2g

Note: This bare cell diagram is for size reference only. Please refer to the tab configurations at the end of this section for available tabs.

BR2450A

■ Dimensions(mm)



Weight:5.0g

Note: This bare cell diagram is for size reference only. Please refer to the tab configurations at the end of this section for available tabs.


■ Specification

Nominal voltage (V)	3
Nominal capacity (mAh)	255
Continuous standard load (mA)	0.03
Operating temperature (C)	-40 ~ +125

■ Specification

Nominal voltage (V)	3
Nominal capacity (mAh)	550
Continuous standard load (mA)	0.03
Operating temperature (C)	-40 ~ +125

■ Temperature Characteristics



■ Temperature Characteristics

