



FEATURES:

- Replaceable tip probe set with spring-loaded pogo-pin triple-point SMD Microtip included. (Other tips are available, see model 6475)
- Fits most DMM's including Fluke, Wavetek Meterman, Greenlee, Amprobe, and others
- Thermoplastic elastomer outer coat provides comfortable grip and flexible strain relief
- Probe and banana plug are molded directly onto the wire for robust pull strength
- Wire is a high strand count silicone wire for extreme flexibility and high temperature resistance
- Banana plug spring is Nickel-plated Beryllium Copper for long insertion life

MATERIALS:

Probe:

Outer Insulation: Santoprene[®] rubber, gray
Inner Insulation: polypropylene, black and red
Tip: Gold-plated Beryllium Copper
Wire: 18 AWG Silicone insulated

Banana Plug: Nickel-plated brass

Spring: Nickel-plated Beryllium Copper

Plug Insulation: Polypropylene, color: one black, one red

RATINGS:

IEC 1010-2-031, Category III 1000V

Operating Voltage: 1000 V

Current: 5 Amperes

ORDERING INFORMATION: Model 6470

Includes a set of one black and one red test lead with two replaceable tips

All dimensions are in inches.

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA