

Double Row Terminal Blocks

Kulka® 600A/800A GP Series

300 Volts AC/DC (Class B)

600A Series only

150 Volts AC/DC (Class C)

600A and 800A Series



600A GP 06

Specifications:

- Base, Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #6-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-22 Poles
- 3/8" Centers
- Wire Range With Wire Binding Screw
#12 - #22 AWG – 15 Amps
- 800A Series (Riveted KT's) - see page 105
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

Kulka® Catalog #	# of poles	Dimensions	
		A	B
600A GP 01	1	1.03	0.75
600A GP 02	2	1.41	1.13
600A GP 03	3	1.78	1.50
600A GP 04	4	2.16	1.88
600A GP 05	5	2.53	2.25
600A GP 06	6	2.91	2.63
600A GP 07	7	3.28	3.00
600A GP 08	8	3.66	3.38
600A GP 09	9	4.03	3.75
600A GP 10	10	4.41	4.13
600A GP 11	11	4.78	4.50
600A GP 12	12	5.16	4.88
600A GP 13	13	5.53	5.25
600A GP 14	14	5.91	5.63
600A GP 15	15	6.28	6.00
600A GP 16	16	6.66	6.38
600A GP 17	17	7.03	6.75
600A GP 18	18	7.41	7.13
600A GP 19	19	7.78	7.50
600A GP 20	20	8.16	7.88
600A GP 21	21	8.53	8.25
600A GP 22	22	8.91	8.63

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #	PRODUCT DESCRIPTION	PAGE REFERENCE
MSP	KULKA	
	KT19	Full Quick Connect (0° Flat)
	KT20	Full Quick Connect (45° Bend)
	KT21	Full Quick Connect (90° Bend)
	KT25	Half Quick Connect (0° Flat)
	KT26	Half Quick Connect (45° Bend)
	KT27	Half Quick Connect (90° Bend)
	ST	Full Solder
	3/4 ST	Half Solder
	Y	Feed Thru Solder (.312)
	YSY	Feed Thru Solder (.500)
	Z	Lug Over the Side (.625)
	J 600	Line to Line Jumper
	600 RJ(S)	Multiple Position Jumper
	3860	Wire Clamp Screw, Brass
	3865	Wire Clamp Screw
	2002	Stud
PSB		Phil-Slot Brass Screw

Quick Connects: .020" x .187"

See pages 104-115 for terminal block accessories

