







RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

.040	1.02		
.035	0.89	.900	22.86
.032	0.81	.535	13.59
.025	0.64	.310	7.87
.020	0.51	.295	7.49
.015	0.38	.225	5.72
.010	0.25	.200	5.08
.009	0.23	.140	3.56
.008	0.20	.130	3.30
.005	0.13	.125	3.18
.003	0.08	.100	2.54
.001	0.03	.063	1.60
.000	0.00	.050	1.27
IN	MM	IN	MM

CONVERSION TABLE

	8	643265-9
OBSOLETE	2,4,6,8	643265-8
	6	643265-7
	4	643265-5
	2	643265-4
OBSOLETE	3	643265-3
	7	643265-2
	POST NUMBER OMITTED	PART NUMBER

643265-2 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG L. SMITH 30MAR93 CHK R. SWING 30MAR93 APVD R. SPEER 15APR93		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± .005 1 PLC ± .005 2 PLC ± .005 3 PLC ± .005 4 PLC ± .005 ANGLES ± 0°30'		NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE STRAIGHT POST, TIN PLATED, 9 POSITION, OMITTED POST	
MATERIAL 7		FINISH 7		WEIGHT —	
CUSTOMER DRAWING		SIZE A1 CAGE CODE 00779 DRAWING NO. C-643265		RESTRICTED TO —	
		SCALE 8:1		SHEET 1 of 1 REV W	