


Premium cable ties with steel locking barb Identification ties


- Identification ties with incorporated label for durable marking and tying
- Label forms onto the bundle for types TY512M, TY51M and protrudes for ties TY532M and TY53M
- Type 51M is MIL (MS-3368-5) approved
- Trouble-free installation
- Simple marking on the roughened writing surface using the special marking pen WT163M-1 (black ink) or WT163M-3 (red ink) - See page 29
- All edges are rounded to make installation easier



TY532M & TY53M



TY512M & TY51M



Technical Information

Material - Moulding	Polyamide 6.6
Material - Locking barb	316 grade stainless steel
Temperature range	-40°C to +85°C
Colour	Natural
Flammability rating	UL 94 V-2
Other properties	Halogen free, Silicone free

Approvals



E49405

Ordering Information

PRODUCT REF.	MIL SPEC.	LENGTH L [mm]	WIDTH W [mm]	THICKNESS [mm]	BUNDLE DIAMETER FROM ... TO [mm]	MINIMUM TENSILE STRENGTH [N]	LABEL DIMENSIONS [mm]	QUANTITY [pieces]	TOOLING
TY51M	MS-3368-5	92	2.4	1.0	10 - 16	80	25.4 x 7.9	500	WT193A ERG299 TR227
TY512M	–	210	2.4	1.0	10 - 51	80	25.4 x 7.9	1000	
TY53M	–	102	2.4	1.0	2 - 16	80	20.6 x 9.3	500	
TY532M	–	212	2.4	1.0	2 - 51	80	20.6 x 9.3	1000	

For other materials and colours contact your Sales Office
For tooling specifications see pages 92 to 99