


HONEYWELL
PART NUMBER

111SM23-H4

PRODUCT CODE
TYJ2301

REV	DOCUMENT	CHANGED BY	CHECK
7	0038225	PRS 04APR08	BLR

.187 DIA X .125 WIDE OIL BRONZE
ROLLER (.005 T.I.R.)



NOTE -
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .087 MAX DIA ON .375 ± .002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.
PR - 4796

REPLACES
-

CHARACTERISTICS

OPERATING FORCE - - - - 7 OZ MAX

RELEASE FORCE - - - - 2 OZ MIN

PRETRAVEL - - - - .219 MAX

DIFFERENTIAL TRAVEL - - .025 MAX

OVERTRAVEL - - - - .030 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	1/2 AMP	1/2 AMP
RESISTIVE	1 AMP	1 AMP

MAXIMUM INRUSH 2 AMP

APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4	UL, CSA	1A, 125 VAC ~	CE	UL	CE
-----------	----------	--------------------	---------	---------------	----	----	----

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±	-
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	-
ANGLES		±	-

THIRD ANGLE PROJECTION



DRAWN	VK	26 OCT 07
CHECK	RJ	26 OCT 07

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	111SM23-H4	7
SCALE	-	WEIGHT .008 LB MAX	SHEET 1 OF 1