



Surface mounting enclosure


Part no. **M22-I12**

Article no. **222688**

Including mounting plate for base fixing

Enclosure base anthracite

Program

Range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Accessories			Surface mounting enclosure
Basic function accessories			Surface mounting enclosure
Single unit/Complete unit			Single unit
Material			Enclosure base anthracite
			Including mounting plate for base fixing
Number of locations		Qty.	12
Colour			
			
RAL Value			RAL 7035
Protection type			IP55
Connection to SmartWire-DT			no

Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	012528
CSA Class No.	3211-03
NA Certification	UL listed, CSA certified
Degree of Protection	UL/CSA Type 3R, 4X, 12, 13


Technical data according to ETIM 4.0

Protection type (IP)			IP67
Number of locations			12
Color housing cover			gray
Openings diameter		mm	22
Housing material			Insulated material
Construction type housing			surface mounting enclosure

CAD-Data

Product standards CAD data: <http://eaton-moeller.partcommunity.com>

Dimensions



Cable entries: 2 x M20, 4 x M20, 2 x M25

Additional product information (links)

AWA1160-1746 (IL04716003Z) RMQ-Titan System	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/17460805.pdf
Engineering	
Key to part numbers	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/TYPENSCHLUESSEL_RM-Q-TITAN_de.pdf
Engineering	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/PRO_RMQTitan_D_de.pdf
Ordering example for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Bestellbeispiel_F0315_COMBINATION_de.pdf
Order form for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf