




WIRE AND CABLE

HOOK UP WIRE



✓ Active

TE CONNECTIVITY (TE)

44A0111-30-7

Raychem | SP

44A0111-30-7

TE Internal Number: 2821703004

Alias ID: 1192107-9

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 44

Voltage Rating (V) 600

Insulation Material Radiation-Crosslinked, Extruded Polyalkene

Conductor Material Tin-Plated Copper

Wire Size (AWG) 30

PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

Customer Drawing

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 44

Product Classification Cable - High Performance - Spec 44, 55 & RCW

Product Type Cable

Cable Style Primary

Configuration Features

Number of Strands 7

Number of Conductors 1

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Insulation Material Radiation-Crosslinked, Extruded Polyalkene

Conductor Material Tin-Plated Copper

Wire Color Violet

Dimensions

Strand Size (AWG) 38

Wire Size (AWG) 30

Wire Size (mm²) .05

Conductor Diameter .31 mm [.012 in]

Wire Diameter .69 mm [.027 in]

Overall Outside Diameter .69 mm [.027 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 150

Other

Wire Source United Kingdom

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF