

RECORD POWER

SHEFFIELD - ENGLAND

DRILL PRESS VICES


DMD PV2

DMD PV3


DMD PV4

Quality and Precision are the hallmarks of the Record Power Drill Press Vice range. Cast in grey iron, a material noted for its high damping capacity and resistance to stress.


Each drill press vice features a two start rolled acme thread to speed the jaws from fully closed to fully open with a minimum of winding, and in addition feature vertical 'V' grooved jaws enabling almost any shape of workpiece to be clamped.




DMD PV2



DMD PV3



DMD PV4



SPECIFICATION CHART	DMD PV2		DMD PV3		DMD PV4	
	inches	mm	inches	mm	inches	mm
Jaw opening (C)	2½	64	3	75	4¾	110
Jaw Width (B)	3	75	4	106	4½	115
Body Length (A)	6⅝	168	8⅞	213		
Slot Length (D)	2¼	56	2⅞	68	4½	115
Distance Between Slots (F)	4¼	108	5⅞	141	6	153
Clamping Force	1.5 ton		2.0 ton		2.0 ton	