



SEE SEPARATE RESTRICTED CUSTOMER
DRAWING WITH THIS PART NUMBER

2. SEE I.S. 1914-2



RECOMMENDED STRIP LENGTH



	OBSOLETE	RG-179/U & 187/U	30.48	[1.200]	220009-1	21427-2	9-328666-0	1-331368-4	2-331355-5	9-225396-2
	OBSOLETE	RG-174/U & 188/U	30.48	[1.200]	220009-1	21427-2	9-328666-0	1-331368-2	2-331355-5	9-225396-1
	OBSOLETE	RG-58/U,58A/U,58B/U & 58C/U	30.48	[1.200]	69478-1	-	9-50427-1	1-331369-6	2-331355-3	9-225396-0
△	SUPERSEDED BY 225396-2	-	-	-	-	-	-	-	-	2-225396-3
△	SUPERSEDED BY 225396-1	-	-	-	-	-	-	-	-	2-225396-2
	SUPERSEDED BY 413779-1	BELDEN 88240,HI-TEMP 58C/U & BERK-TEK BTDC 58	35.56	[1.400]	69478-1	-	9-228783-0	1-331369-6	2-331355-3	2-225396-1
	△OBSOLETE	-	-	-	-	-	-	-	-	2-225396-0
	OBSOLETE	BELDEN 9209 & TIMES FIBER AA2992	30.48	[1.200]	69477-1	-	9-50428-0	2-331368-3	2-331355-7	1-225396-9
	SUPERSEDED BY 225396-8	-	-	-	-	-	-	-	-	1-225396-3
	SUPERSEDED BY 413779-5	RG-180/U,180A/U & 195/U	30.48	[1.200]	69477-2	-	9-329461-0	1-331368-4	2-331355-5	225396-9
	OBSOLETE	RG-179/U & 187/U	30.48	[1.200]	220009-1	21427-2	9-328666-0	1-331368-4	2-331355-5	225396-8
		RG-174/U & 188/U	30.48	[1.200]	220009-1	21427-2	9-328666-0	1-331368-2	2-331355-5	225396-7
	SUPERSEDED BY 2-331351-9	-	-	-	-	-	-	-	-	225396-6
	OBSOLETE	-	-	-	-	-	-	-	-	225396-3
		RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	30.48	[1.200]	69477-1	-	9-50428-0	2-331368-3	2-331355-4	225396-2
		RG-58/U,58A/U,58B/U & 58C/U	30.48	[1.200]	69478-1	-	9-50427-1	1-331369-6	2-331355-3	225396-1
		CABLE SIZE	A		CRIMP TOOL	④ BUSHING QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① JACK ASSY QTY=1	PART NUMBER