





NOTE:

1. MATERIAL:

HOUSING: PA46 GLASS FILLED, UL94V-0, COLOR: NATURAL

TERMINAL: PHOSPHOR BRONZE

2. PLATING: 1) PARTIAL GOLD PLATING OVER NICKEL PLATING OVERALL

CONTACT POINT: 0.10 μm MINIMUM GOLD PLATING



TAIL POINT :GOLD PLATING

2) 1-3 μm TIN-BISMUTH OVER NICKEL PLATING OVERALL

3. PRODUCT SPECIFICATION: PS-78119-001

4. PRODUCT ARE PACKED IN TAPE & REEL.


REVISED EC NO: J2013-1512 DRAWN: AYOUSHI 101 CHKD: K TAKAHASHI APPR: YNOGAWA	DESCRIPTION REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
					DRAWN BY DATE		TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT								
					CHECKED BY DATE										
					APPROVED BY DATE		molex								
					MATERIAL NO.							DOCUMENT NO.		SHEET NO.	
					SIZE							SD-78119-001		1 OF 7	
A4		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											




N	0.30 ^{+0.05} _{-0.02}	0.30 ^{+0.05} _{-0.02}	0.35 ^{+0.04} _{-0.03}	0.35 ^{+0.05} ₀
P	0.50±0.03	0.50±0.05	0.50±0.02	0.50±0.05
M	0.50±0.10	0.50±0.08	0.50±0.12	0.50±0.10
B	B±0.03	B±0.05	B±0.03	B±0.05
	1	2	1	2
	FFC		FPC	

REVISED EC NO: J2013-1512 DRWN: KAWASHI 101 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/25	DESCRIPTION	QUALITY SYMBOLS ▽_F=0 ▽_G=0 ▽_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT					
					CHECKED BY BOKOK	DATE 2006/04/18						
					APPROVED BY PTLIM		DATE 2006/04/18	molex				
					MATERIAL NO.		DOCUMENT NO.					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		ANGULAR ± 3 °		SEE TABLE		SD-78119-001		2 OF 7				
A4	REV		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

EMBOSSED TYPE A





CUSTOMER
PULL OUT DIRECTION



REEL

NOTES:



1. LEADER AND TRAILER TAPE

2. PEELING OFF FORCE OF THE TOP TAPE: 20-80gf.
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)

3. PACKAGING STANDARD IS AS PER EIA-481.


4. TAPE & REEL QUANTITY = 1000 PCS/REEL

SECTION Y-Y




DETAIL 1

EMBOSSED TYPE B



DETAIL 1



SECTION Z-Z

REVISED	EC NO: J2013-1512	DRWN:AYOSHI/01	2013/06/12	CHKD:K TAKAHASHI	2013/06/12	APPR:YNOGAWA	2013/06/25	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
										MM ONLY		NTS	METRIC	◎ □					
												DRAWN BY	DATE	TITLE					
												CHECKED BY	DATE	0.50MM PITCH, FPC CONN. NON-ZIF, SMT					
												APPROVED BY	DATE						
A4	REV								F _A =0 F _G =0 F _P =0	4 PLACES	± ---	± ---	YLOIAO	2006/04/11	molex				
										3 PLACES	± ---	± ---	BOKOK	2006/04/18					
										2 PLACES	± 0.15	± ---	PTLIM	2006/04/18					
										ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
										DRAFT WHERE APPLICABLE		SEE TABLE		SD-78119-001		5 OF 7			
										MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																
	ELV & RoHS COMPLIANT																																																																																																																																																																																																																																																																																									
F											F																																																																																																																																																																																																																																																																															
E	PARTIAL GOLD PLATING TERMINAL ASSEMBLY PART NUMBERS										E																																																																																																																																																																																																																																																																															
D	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1108</td><td>78119-0108</td><td>10</td><td>24.00</td><td>-</td><td>11.50</td><td>7.40</td><td>5.10</td><td rowspan="10">A</td></tr><tr><td>78119-1118</td><td>78119-0118</td><td>11</td><td>24.00</td><td>-</td><td>11.50</td><td>7.90</td><td>5.60</td></tr><tr><td>78119-1128</td><td>78119-0128</td><td>12</td><td>24.00</td><td>-</td><td>11.50</td><td>8.40</td><td>6.10</td></tr><tr><td>78119-1138</td><td>78119-0138</td><td>13</td><td>24.00</td><td>-</td><td>11.50</td><td>8.90</td><td>6.60</td></tr><tr><td>78119-1148</td><td>78119-0148</td><td>14</td><td>24.00</td><td>-</td><td>11.50</td><td>9.40</td><td>7.10</td></tr><tr><td>78119-1158</td><td>78119-0158</td><td>15</td><td>24.00</td><td>-</td><td>11.50</td><td>9.90</td><td>7.60</td></tr><tr><td>78119-1168</td><td>78119-0168</td><td>16</td><td>24.00</td><td>-</td><td>11.50</td><td>10.40</td><td>8.10</td></tr><tr><td>78119-1178</td><td>78119-0178</td><td>17</td><td>24.00</td><td>-</td><td>11.50</td><td>10.90</td><td>8.60</td></tr><tr><td>78119-1188</td><td>78119-0188</td><td>18</td><td>24.00</td><td>-</td><td>11.50</td><td>11.40</td><td>9.10</td></tr><tr><td>78119-1198</td><td>78119-0198</td><td>19</td><td>24.00</td><td>-</td><td>11.50</td><td>11.90</td><td>9.60</td></tr><tr><td>78119-1208</td><td>78119-0208</td><td>20</td><td>24.00</td><td>-</td><td>11.50</td><td>12.40</td><td>10.10</td><td rowspan="10">B</td></tr><tr><td>78119-1218</td><td>78119-0218</td><td>21</td><td>32.00</td><td>28.40</td><td>14.20</td><td>12.90</td><td>10.60</td></tr><tr><td>78119-1228</td><td>78119-0228</td><td>22</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.40</td><td>11.10</td></tr><tr><td>78119-1238</td><td>78119-0238</td><td>23</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.90</td><td>11.60</td></tr><tr><td>78119-1248</td><td>78119-0248</td><td>24</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.40</td><td>12.10</td></tr><tr><td>78119-1258</td><td>78119-0258</td><td>25</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.90</td><td>12.60</td></tr><tr><td>78119-1268</td><td>78119-0268</td><td>26</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.40</td><td>13.10</td></tr><tr><td>78119-1278</td><td>78119-0278</td><td>27</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.90</td><td>13.60</td></tr><tr><td>78119-1288</td><td>78119-0288</td><td>28</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.40</td><td>14.10</td></tr><tr><td>78119-1298</td><td>78119-0298</td><td>29</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.90</td><td>14.60</td></tr><tr><td>78119-1308</td><td>78119-0308</td><td>30</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.40</td><td>15.10</td></tr></table>								ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A	78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60	78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10	78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60	78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10	78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60	78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10	78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60	78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10	78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60	78119-1208	78119-0208	20	24.00	-	11.50	12.40	10.10	B	78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60	78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10	78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60	78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10	78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60	78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10	78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60	78119-1288	78119-0288	28	32.00	28.40	14.20	16.40	14.10	78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60	78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1318</td><td>78119-0318</td><td>31</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.90</td><td>15.60</td><td rowspan="12">B</td></tr><tr><td>78119-1328</td><td>78119-0328</td><td>32</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.40</td><td>16.10</td></tr><tr><td>78119-1338</td><td>78119-0338</td><td>33</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.90</td><td>16.60</td></tr><tr><td>78119-1348</td><td>78119-0348</td><td>34</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.40</td><td>17.10</td></tr><tr><td>78119-1358</td><td>78119-0358</td><td>35</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.90</td><td>17.60</td></tr><tr><td>78119-1368</td><td>78119-0368</td><td>36</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.40</td><td>18.10</td></tr><tr><td>78119-1378</td><td>78119-0378</td><td>37</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.90</td><td>18.60</td></tr><tr><td>78119-1388</td><td>78119-0388</td><td>38</td><td>32.00</td><td>28.40</td><td>14.20</td><td>21.40</td><td>19.10</td></tr><tr><td>78119-1398</td><td>78119-0398</td><td>39</td><td>44.00</td><td>40.40</td><td>20.20</td><td>21.90</td><td>19.60</td></tr><tr><td>78119-1408</td><td>78119-0408</td><td>40</td><td>44.00</td><td>40.40</td><td>20.20</td><td>22.40</td><td>20.10</td></tr></table>		ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B	78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10	78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60	78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10	78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60	78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10	78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60	78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10	78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60	78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10			C
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																																		
78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A																																																																																																																																																																																																																																																																																		
78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60																																																																																																																																																																																																																																																																																			
78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10																																																																																																																																																																																																																																																																																			
78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60																																																																																																																																																																																																																																																																																			
78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10																																																																																																																																																																																																																																																																																			
78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60																																																																																																																																																																																																																																																																																			
78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10																																																																																																																																																																																																																																																																																			
78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60																																																																																																																																																																																																																																																																																			
78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10																																																																																																																																																																																																																																																																																			
78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60																																																																																																																																																																																																																																																																																			
78119-1208	78119-0208	20	24.00	-	11.50	12.40	10.10	B																																																																																																																																																																																																																																																																																		
78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60																																																																																																																																																																																																																																																																																			
78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10																																																																																																																																																																																																																																																																																			
78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60																																																																																																																																																																																																																																																																																			
78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10																																																																																																																																																																																																																																																																																			
78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60																																																																																																																																																																																																																																																																																			
78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10																																																																																																																																																																																																																																																																																			
78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60																																																																																																																																																																																																																																																																																			
78119-1288	78119-0288	28	32.00	28.40	14.20	16.40	14.10																																																																																																																																																																																																																																																																																			
78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60																																																																																																																																																																																																																																																																																			
78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10																																																																																																																																																																																																																																																																																			
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																																		
78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B																																																																																																																																																																																																																																																																																		
78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10																																																																																																																																																																																																																																																																																			
78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60																																																																																																																																																																																																																																																																																			
78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10																																																																																																																																																																																																																																																																																			
78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60																																																																																																																																																																																																																																																																																			
78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10																																																																																																																																																																																																																																																																																			
78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60																																																																																																																																																																																																																																																																																			
78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10																																																																																																																																																																																																																																																																																			
78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60																																																																																																																																																																																																																																																																																			
78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10																																																																																																																																																																																																																																																																																			
B											B																																																																																																																																																																																																																																																																															
A	<table><tr><td rowspan="5">REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 CHKD: K TAKAHASHI APPR: YNOGAWA 2013/06/12 2013/06/12 2013/06/15</td><td colspan="2">QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td colspan="2">$F_A=0$</td><td colspan="2"><table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.15</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table></td><td colspan="2"><table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>YLQIAO</td><td>2006/04/11</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>BOKOK</td><td>2006/04/18</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>PTLIM</td><td>2006/04/18</td></tr></table></td><td colspan="2">TITLE</td><td colspan="2">0.50MM PITCH, FPC CONN. NON-ZIF, SMT</td></tr><tr><td colspan="2">$F_B=0$</td><td colspan="2">ANGULAR ± 3 °</td><td colspan="2">MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td colspan="2">$F_C=0$</td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-78119-001</td><td colspan="2">6 OF 7</td></tr><tr><td colspan="2">$F_D=0$</td><td colspan="2"></td><td colspan="2">SIZE A3</td><td colspan="4">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>										REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 CHKD: K TAKAHASHI APPR: YNOGAWA 2013/06/12 2013/06/12 2013/06/15	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		$F_A=0$		<table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.15</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>			mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.15	± ---	1 PLACE	± ---	± ---	0 PLACE	±	±	<table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>YLQIAO</td><td>2006/04/11</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>BOKOK</td><td>2006/04/18</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>PTLIM</td><td>2006/04/18</td></tr></table>		DRAWN BY	DATE	YLQIAO	2006/04/11	CHECKED BY	DATE	BOKOK	2006/04/18	APPROVED BY	DATE	PTLIM	2006/04/18	TITLE		0.50MM PITCH, FPC CONN. NON-ZIF, SMT		$F_B=0$		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		$F_C=0$		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-78119-001		6 OF 7		$F_D=0$				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				A																																																																																																																																																																																														
REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 CHKD: K TAKAHASHI APPR: YNOGAWA 2013/06/12 2013/06/12 2013/06/15	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																																																																																																																																																																																																	
	$F_A=0$		<table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.15</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>			mm	INCH	4 PLACES	± ---	± ---		3 PLACES	± ---	± ---	2 PLACES	± 0.15	± ---	1 PLACE	± ---	± ---	0 PLACE	±	±	<table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>YLQIAO</td><td>2006/04/11</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>BOKOK</td><td>2006/04/18</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>PTLIM</td><td>2006/04/18</td></tr></table>		DRAWN BY	DATE	YLQIAO	2006/04/11	CHECKED BY	DATE	BOKOK	2006/04/18	APPROVED BY	DATE	PTLIM	2006/04/18	TITLE		0.50MM PITCH, FPC CONN. NON-ZIF, SMT																																																																																																																																																																																																																																																		
		mm	INCH																																																																																																																																																																																																																																																																																							
	4 PLACES	± ---	± ---																																																																																																																																																																																																																																																																																							
	3 PLACES	± ---	± ---																																																																																																																																																																																																																																																																																							
2 PLACES	± 0.15	± ---																																																																																																																																																																																																																																																																																								
1 PLACE	± ---	± ---																																																																																																																																																																																																																																																																																								
0 PLACE	±	±																																																																																																																																																																																																																																																																																								
DRAWN BY	DATE																																																																																																																																																																																																																																																																																									
YLQIAO	2006/04/11																																																																																																																																																																																																																																																																																									
CHECKED BY	DATE																																																																																																																																																																																																																																																																																									
BOKOK	2006/04/18																																																																																																																																																																																																																																																																																									
APPROVED BY	DATE																																																																																																																																																																																																																																																																																									
PTLIM	2006/04/18																																																																																																																																																																																																																																																																																									
$F_B=0$		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.																																																																																																																																																																																																																																																																																		
$F_C=0$		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-78119-001		6 OF 7																																																																																																																																																																																																																																																																																		
$F_D=0$				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																																																																																				
	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																																	

