



# THA-540

## フラッシュハンドル

Flush Handle Latch



### 特長

THA-408AN シリーズの鍵番号 No.2200 及び No.200 仕様品です。ドライバー等による不正開錠が困難なシリンダー錠タイプの平面ハンドルです。

### 用途

配電盤・分電盤・OA 機器・筐体等


### 仕様

本品は止め金具の組替えによる左右兼用型です。キーの回転は 90° 回転です（2 点抜き）。止め金具は TO-300 シリーズも使用可能です。


### ■部品表 Parts List

部番 No.	部品名 Part Name	材質 Material	処理 Finish	数 Quantity
1	ベース Base	ZDC	Cr(サチライト) Cr (Satellite Chrome Plating)	1
2	ハンドル Handle			1
3	ラッチ Latch			1
4	ラッチカバー Latch Cover	SUS304	バレル研磨 Barrel Polishing	1
5	止め金具 Cam	SPCC		1
6	座金組込十字穴付なべ小ねじ Cross Hole Pan Head Screw with Washer	S		2
7	ワン型ワッシャー Pan Shaped Washer	SPCE		2
8	十字穴付なべ小ねじ Cross Hole Countersunk Screw	S		2
9	ロック Lock	SUS/ZDC	- / 3 値クロメート Trivalent Chromate Treatment	1
10	キー Key	C3713	Ni	2

### THA-540-1K・1



### THA-540-2K・2



本図は鍵付を示したものです。  
The figure shows the handle with key.

### Characteristic


Cylinder key type flush handle which is difficult to open the key illegally. Two types of keys are available, No.2200 and No. 200.

### Application


Distribution boards / Distribution panels / Office automation appliances / Various types of boxes, etc.

### Specification

It can be used for both right and left swing type by changing the position of the cam. Turning angle of key is 90°. TO-300 series cam can be used.



### THA-540-3K・3



本図は鍵付を示したものです。  
The figure shows the handle with key.

### 仕様 Specification

型番 Model No.	鍵番号 Key No.	適用板厚 Applicable Panel Thickness	自重(g) Net Weight(g)	価格(円) Price(yen)
THA-540-1K	No.2200/No.200	t0.6 ~ t3.2	354	¥1,350
THA-540-1	鍵ナシ Without Key		346	¥1,150
THA-540-2K	No.2200/No.200	t0.6 ~ t2.3	214	¥1,150
THA-540-2	鍵ナシ Without Key		202	¥950
THA-540-3K	No.2200/No.200		160	¥1,080
THA-540-3	鍵ナシ Without Key		146	¥820

特注品のご相談承ります Please contact us for custom-made.