

T-2¼ SINGLE CONTACT BAYONET BASE


XENON GAS FILLED LAMP

28V 10W

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE
WL-998502-20	T-2¼	BA15s	28V 10W	CC-8

TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX	
28V	.324	.360	.396	6.97	8.20	9.43	7,000

DIMENSIONAL CHARACTERISTICS



NOTES

1. High temperature solder (95% tin, 5% silver), softening point 221°C
2. Part mark WL-998502-20, 28V, 10W
3. RoHS compliant

