


342A138-3-0 Product Details

 Share  Print  Email



342A138-3-0

TE Internal Number: 823466-000

 Obsolete

[Contact Product Information Center](#)

Molded Parts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Molded Part Type = Transition
- Family Name = 342A1
- Transition Type = 45° Side-Breakout
- 2 Branches/Legs
- General Purpose Application

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [Transition, 45 Degrees](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Molded Part Type = Transition
- Size = 38
- Material = Semi rigid Modified Polyolefin

Body Features:

- Transition Type = 45° Side-Breakout
- Number of Branches/Legs = 2
- 1st Branch/Leg Range (mm [in]) = 12.40 - 26.90 [0.488 - 1.059]
- 2nd Branch/Leg Range (mm [in]) = 12.40 - 26.90 [0.488 - 1.059]

Contact Features:

- [Family Name](#) = 342A1

Housing Features:

- [Material Systems Code](#) = 10
- Adhesive Pre-Coating = Without
- Adhesive Description = Adhesive Purchased Separately.
- Max. Inside Diameter of Part (mm [in]) = 25.40 - 55.60 [1.000 - 2.189]

Configuration Features:

- Material Code = 3
- Adhesive Code = S1125

Industry Standards:

- Government/Industry Qualification = No
- Approved Standards = DEF Std 59-97 Issue 3 Type DA, MIL-I-81765/1 Class I, UL224 E85831
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -55 - +135

Operation/Application:

- Application = General Purpose

Other:

- Brand = Raychem
- Comment = Contact Raychem for additional adhesive and/or cut off boot length information

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

