



MATERIALS:
 INSULATOR: P. B. T. 30% GLASS FIBER, UL94V-0
 CONTACT MATERIAL: BRASS OR PHOSPHOR BRONZE,
 UNDERPLATED: NICKEL
 CONTACT AREA: 1u" - 30u" SELECTIVE GOLD
ELECTRICAL:
 CURRENT RATING: 1AMP.
 INSULATION RESISTANCE: 1000MΩ MIN.
 DIELECTRIC WITHSTANDING: 500VAC
 OPERATING TEMPERATURE: -55°C - +105°C

AWLP-xx/3.2-x-R

T - TIN
 G - GOLD

OF CONTACTS
 (6 - 64)

POSITION	A	B	POSITION	A	B
6P	12.94	5.08	26P	38.40	30.48
8P	15.48	07.62	28P	40.60	33.02
10P	18.10	10.16	30P	43.50	35.56
12P	20.51	12.70	34P	48.58	40.64
14P	23.05	15.24	40P	56.20	48.26
16P	25.64	17.78	50P	69.00	60.96
18P	28.15	20.32	60P	81.75	73.66
20P	30.78	22.86	64P	86.83	78.74
24P	35.86	27.94			

UNLESS OTHERWISE SPECIFIED TOLERANCE ±0.2		ASSMANN Electronic Components	
SCALE: AS SHOWN	UNIT: mm	DRAWN NAME: TRANSITION PLUG (PITCH: 2.54 mm) 1/3	
DRAWN JOE	12/16/05		
CHECKED	/ /		
APPROVED	/ /	PRODUCT NO.	AWLP-xx/3.2-x-R
DATE	12/14/05	FILE NAME:	

REV. A ECN-0512100(Emily)

REV. DESCRIPTION DATE SIZE REV. A