





ELECTRICAL SPECS:

- 1. LIFE: 10,000 INSERTION/WITHDRAWAL CYCLE MINIMUM
- 2. CONTACT RESISTANCE: 50m Ω MAXIMUM
- 3. INSULATION RESISTANCE: 1000m Ω MINIMUM
- 4. DIELECTRIC WITHSTANDING VOLTAGE: 500AC MAXIMUM
- 5. MAXIMUM RATING: 5A, 12V DC



SCHEMATIC DIAGRAM

Date	SYM	REVISION RECORD	AUTH	DR	CK
05/08/04	A	ADDED ELECTRICAL SPECS	T.B.	B.S.	

ITEM NO.	PART NAME	MATL. SPECIFICATION	Tolerance (Inches)	 Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
1	PIN TERMINAL	0.4 THK BRASS, SILVER PLTD.				
2	SLEEVE SPRING	0.2 THK PHOSPHORSCENT BRONZE, SILVER PLTD.	Decimal ±.5 (.020)		Scale	Drawn By B.S.
3	BREAK TERMINAL	0.3 THK BRASS, SILVER PLTD.				Approved By T.B.
4	PIN (Ø2.1)	COPPER, NICKLE PLTD.				
5	HOUSING	BLACK, P.B.T.	Fractional ± .8 (.030)	Title DC JACK - PANEL MOUNT TYPE		
6	INSULATOR	BAKELITE, NATURAL				
			Angular ± 3°	Date 05/08/04	Drawing Number EJ504B	