

4		3		2		1							
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS					
© COPYRIGHT — By —		ALL RIGHTS RESERVED.		G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
									D1	REVISED PER ECO-14-019230	02APR2015	NK	DR

D

C

B

A

1 FOR .115 TO .170 WIRE INSULATION DIA.

.760 MAX

AMP AMP AMP

SERRATIONS

INSULATION

BODY

1000	LOOSE PIECE	INSULATION: PVC COLOR: BLUE BODY: COPPER (QQ-C-576) TIN PLATE PER ASTM B-545		34134
QTY	PACKAGE TYPE	MATERIAL / FINISH		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

DWN
jr ruth
CHK
T MICHIELUTTI
APVD
T MICHIELUTTI

05SEP03
05SEP03
05SEP03

DIMENSIONS:
INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± .005
4 PLC ± —
ANGLES ± 1°

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN
jr ruth
CHK
T MICHIELUTTI
APVD
T MICHIELUTTI

05SEP03
05SEP03
05SEP03

PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
—

NAME
WIRE SPLICE, PARALLEL,
PLASTI-GRIP, WIRE SIZE :16-14

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-34134

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
D1

1470-19 (3/11)