

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.6V00
15	39.14	33.32	25.18	24.54	19.18	D15S24B.6V00
25	53.03	47.04	39.12	38.25	33.12	D25S24B.6V00
37	69.32	63.50	55.68	54.71	49.68	D37S24B.6V00

Plating: 6 $\rightarrow$ 0.76 μ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09524B.6V00L
15	39.14	33.32	25.18	24.54	19.18	D15524B.6V00L
25	53.03	47.04	39.12	38.25	33.12	D25524B.6V00L
37	69.32	63.50	55.68	54.71	49.68	D37524B.6V00L

Plating: 6 $\rightarrow$ 0.76 μ AU

Pitch 2.76 (shell 25-37)
Pitch 2.74 (shell 09-15)

$\phi 0.13$ holes $\phi 0.90$ mini

$\phi 3.10 \pm 0.10$

$\phi 0.13$

1.37 (shell 09-15)
1.36 (shell 25-37)

1.42

1.42


E

B

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:	
SEE DRAWING C01-8646-0000	

European Views

rev	ecn no	dr	date
B	-	-	1996/09/05
D	LS05-001	MPE	2005/03/10
E	LS05-0056	MPE	2005/06/24
F	LS06-0097	LGO	2006/07/25
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	LELEON	1992/09/16	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2			
Eng	PESSON	1992/09/16			0.XX	±0.1					
Chr	LEGARE	1992/09/16			0.XX' ±2'	0.XXX		±0.1	ECN LS06-0097		
Appr	LEGARE	1992/09/16	Product family				D-SUB	Spec ref -			
			FEMALE CONNECTOR STD EURO				dwg no C01-8646-0124			Rev F	
title straight solder type for											
catalog no			-				CUSTOMER		sheet 1 of 1		