

Self Laminating Wire And Cable Markers

• B-427 Self-Laminating Vinyl

Labels - Labels with superior chemical and abrasion resistance. Non-printed clear area wraps around and overlaminates the printed text.




Figure 29




Figure 42




Figure 43



Diagram	Catalog #	B#	Color	Approx. Wire Gauge	Label Width A (mm)	Label Height B (mm)	Print-On Height C (mm)	Labels Per Roll	Rec. Ribbon
B-427 Self-Laminating Vinyl Labels									
Fig. 42	M71-10-427	B-427	White	16-10	0.250 (6.4)	0.750 (19.1)	0.375 (9.530)	750	M71-R4300
Fig. 42	BM71-11-427*	B-427	White	16-10	0.500 (12.7)	0.750 (19.1)	0.375 (9.530)	5000	M71-R4300
Fig. 42	M71-11-427	B-427	White	16-10	0.500 (12.7)	0.750 (19.1)	0.375 (9.530)	500	M71-R4300
Fig. 42	M71-96-427	B-427	White	16-10	1.000 (25.4)	0.750 (19.1)	0.375 (9.530)	250	M71-R4300
Fig. 29	M71-30-427-AW	B-427	White	10-4	1.500 (38.1)	0.750 (19.1)	—	250	M71-R4300
Fig. 42	BM71-17-427*	B-427	White	12-10	0.500 (12.7)	1.000 (25.4)	0.375 (9.530)	5000	M71-R4300
Fig. 42	M71-17-427	B-427	White	12-10	0.500 (12.7)	1.000 (25.4)	0.375 (9.530)	500	M71-R4300
Fig. 42	BM71-18-427*	B-427	White	10-4	0.750 (19.1)	1.000 (25.4)	0.375 (9.530)	2500	M71-R4300
Fig. 42	M71-18-427	B-427	White	10-4	0.750 (19.1)	1.000 (25.4)	0.375 (9.530)	250	M71-R4300
Fig. 42	BM71-19-427*	B-427	White	12-10	1.000 (25.4)	1.000 (25.4)	0.375 (9.530)	2500	M71-R4300
Fig. 42	M71-19-427	B-427	White	12-10	1.000 (25.4)	1.000 (25.4)	0.375 (9.530)	250	M71-R4300
Fig. 42	M71-19-427-YL	B-427	Yellow	12-10	1.000 (25.4)	1.000 (25.4)	0.375 (9.530)	250	M71-R4300
Fig. 42	M71-104-427	B-427	White	12-10	1.500 (38.1)	1.000 (25.4)	0.375 (9.530)	250	M71-R4300
Fig. 42	M71-103-427	B-427	White	10-4	1.000 (25.4)	1.250 (31.8)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-28-427	B-427	White	10-4	0.250 (6.4)	1.500 (38.1)	0.500 (12.700)	750	M71-R4300
Fig. 42	BM71-29-427*	B-427	White	10-4	0.500 (12.7)	1.500 (38.1)	0.500 (12.700)	5000	M71-R4300
Fig. 42	M71-29-427	B-427	White	10-4	0.500 (12.7)	1.500 (38.1)	0.500 (12.700)	500	M71-R4300
Fig. 42	BM71-30-427*	B-427	White	10-4	0.750 (19.1)	1.500 (38.1)	0.500 (12.700)	2500	M71-R4300
Fig. 42	M71-30-427	B-427	White	10-4	0.750 (19.1)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-30-427-BL	B-427	Blue	10-4	0.750 (19.1)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-30-427-PL	B-427	Purple	10-4	0.750 (19.1)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-30-427-RD	B-427	Red	10-4	0.750 (19.1)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	BM71-31-427*	B-427	White	10-4	1.000 (25.4)	1.500 (38.1)	0.500 (12.700)	2500	M71-R4300
Fig. 42	M71-31-427	B-427	White	10-4	1.000 (25.4)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-31-427-GN	B-427	Green	10-4	1.000 (25.4)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-31-427-RD	B-427	Red	10-4	1.000 (25.4)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-31-427-YL	B-427	Yellow	10-4	1.000 (25.4)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	BM71-32-427*	B-427	White	10-4	1.500 (38.1)	1.500 (38.1)	0.500 (12.700)	1000	M71-R4300
Fig. 42	M71-32-427-YL	B-427	Yellow	10-4	1.500 (38.1)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-32-427	B-427	White	10-4	1.500 (38.1)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	M71-88-427	B-427	White	10-4	1.750 (44.5)	1.500 (38.1)	0.500 (12.700)	250	M71-R4300
Fig. 42	BM71-107-427*	B-427	White	10-4	2.000 (50.8)	1.500 (38.1)	0.500 (12.700)	1000	M71-R4300
Fig. 42	M71-107-427	B-427	White	10-4	2.000 (50.8)	1.500 (38.1)	0.500 (12.700)	100	M71-R4300
Fig. 42	BM71-21-427*	B-427	White	Cables	1.000 (25.4)	2.500 (63.5)	0.750 (19.050)	1000	M71-R4300
Fig. 42	M71-21-427	B-427	White	Cables	1.000 (25.4)	2.500 (63.5)	0.750 (19.050)	100	M71-R4300
Fig. 42	M71-21-427-YL	B-427	Yellow	Cables	1.000 (25.4)	2.500 (63.5)	0.750 (19.050)	100	M71-R4300
Fig. 42	M71-66-427	B-427	White	Cables	1.938 (49.2)	3.150 (80.0)	1.000 (25.400)	100	M71-R4300
Fig. 43	BM71-64-427*	B-427	White	Cables	1.000 (25.4)	3.375 (85.7)	1.125 (28.580)	1000	M71-R4300
Fig. 43	M71-64-427	B-427	White	Cables	1.000 (25.4)	3.375 (85.7)	1.125 (28.580)	100	M71-R4300
Fig. 42	BM71-23-427*	B-427	White	Cables	1.000 (25.4)	4.000 (101.6)	1.000 (25.400)	1000	M71-R4300
Fig. 42	M71-23-427	B-427	White	Cables	1.000 (25.4)	4.000 (101.6)	1.000 (25.400)	100	M71-R4300
Fig. 42	BM71-109-427*	B-427	White	Cables	1.500 (38.1)	4.000 (101.6)	1.500 (38.100)	500	M71-R4300
Fig. 42	BM71-33-427*	B-427	White	Cables	1.500 (38.1)	4.000 (101.6)	1.000 (25.400)	500	M71-R4300
Fig. 42	M71-109-427	B-427	White	Cables	1.500 (38.1)	4.000 (101.6)	1.500 (38.100)	100	M71-R4300
Fig. 42	M71-33-427	B-427	White	Cables	1.500 (38.1)	4.000 (101.6)	1.000 (25.400)	100	M71-R4300
Fig. 42	M71-33-427-YL	B-427	Yellow	Cables	1.500 (38.1)	4.000 (101.6)	1.000 (25.400)	100	M71-R4300
Fig. 42	BM71-34-427*	B-427	White	Cables	1.500 (38.1)	6.000 (152.4)	1.500 (38.100)	500	M71-R4300
Fig. 42	M71-34-427	B-427	White	Cables	1.500 (38.1)	6.000 (152.4)	1.500 (38.100)	50	M71-R4300

* Bulk roll.

Approx. wire gauge based on AWG for THHN wire.