




FASTENERS

## RETAINING WASHERS

Buy One  
or  
Buy Bulk & SAVERW Series  
Retaining Washers


## Specifications:

- Material: Nylon
- Color: Natural

## Features:

- I.D. designed to grip outside of screw shank
- Easily slides on to the screw but is retained by the screw once assembled
- Used in applications requiring pre-assembly of the screw and washer
- Reduces assembly time and cost

| Item No.  | Screw Size | A     |       | B     |       | C     |      | D     |       | Pack Qty. |
|-----------|------------|-------|-------|-------|-------|-------|------|-------|-------|-----------|
|           |            | In    | mm    | In    | mm    | In    | mm   | In    | mm    |           |
| RW2032A   | #2         | 0.203 | 5.16  | 0.115 | 2.92  | 0.032 | 0.81 | 0.078 | 1.98  | 1,000     |
| RW2062A   | #2         | 0.203 | 5.16  | 0.115 | 2.92  | 0.062 | 1.57 | 0.078 | 1.98  | 1,000     |
| RW4032A   | #4         | 0.265 | 6.73  | 0.156 | 3.96  | 0.032 | 0.81 | 0.102 | 2.59  | 1,000     |
| RW4050A   | #4         | 0.250 | 6.35  | 0.156 | 3.96  | 0.050 | 1.27 | 0.102 | 2.59  | 1,000     |
| RW4062A   | #4         | 0.265 | 6.73  | 0.156 | 3.96  | 0.062 | 1.57 | 0.102 | 2.59  | 1,000     |
| RW4125A   | #4         | 0.265 | 6.73  | 0.156 | 3.96  | 0.125 | 3.18 | 0.102 | 2.59  | 1,000     |
| RW6032A   | #6         | 0.328 | 8.33  | 0.198 | 5.03  | 0.032 | 0.81 | 0.128 | 3.25  | 1,000     |
| RW6062A   | #6         | 0.328 | 8.33  | 0.198 | 5.03  | 0.062 | 1.57 | 0.128 | 3.25  | 1,000     |
| RW7062A   | #7         | 0.750 | 19.05 | 0.375 | 9.53  | 0.062 | 1.57 | 0.215 | 5.46  | 1,000     |
| RW8032A   | #8         | 0.390 | 9.91  | 0.235 | 5.97  | 0.032 | 0.81 | 0.152 | 3.86  | 1,000     |
| RW8045A   | #8         | 0.453 | 11.51 | 0.218 | 5.54  | 0.045 | 1.14 | 0.135 | 3.43  | 1,000     |
| RW8062A   | #8         | 0.390 | 9.91  | 0.235 | 5.97  | 0.062 | 1.57 | 0.152 | 3.86  | 1,000     |
| RW10032A  | #10        | 0.453 | 11.51 | 0.277 | 7.04  | 0.032 | 0.81 | 0.177 | 4.50  | 1,000     |
| RW10062A  | #10        | 0.453 | 11.51 | 0.277 | 7.04  | 0.062 | 1.57 | 0.177 | 4.50  | 1,000     |
| RW250032A | 1/4        | 0.593 | 15.06 | 0.375 | 9.53  | 0.032 | 0.81 | 0.234 | 5.94  | 1,000     |
| RW250062A | 1/4        | 0.593 | 15.06 | 0.375 | 9.53  | 0.062 | 1.57 | 0.234 | 5.94  | 1,000     |
| RW312032A | 5/16       | 0.734 | 18.64 | 0.470 | 11.94 | 0.032 | 0.81 | 0.292 | 7.42  | 1,000     |
| RW312062A | 5/16       | 0.734 | 18.64 | 0.470 | 11.94 | 0.062 | 1.57 | 0.292 | 7.42  | 1,000     |
| RW375032A | 3/8        | 0.890 | 22.61 | 0.564 | 14.33 | 0.032 | 0.81 | 0.350 | 8.89  | 1,000     |
| RW375062A | 3/8        | 0.890 | 22.61 | 0.564 | 14.33 | 0.062 | 1.57 | 0.350 | 8.89  | 1,000     |
| RW437032A | 7/16       | 1.031 | 26.19 | 0.570 | 14.48 | 0.032 | 0.81 | 0.410 | 10.41 | 500       |
| RW437062A | 7/16       | 1.031 | 26.19 | 0.570 | 14.48 | 0.062 | 1.57 | 0.410 | 10.41 | 500       |
| RW500032A | 1/2        | 1.125 | 28.58 | 0.690 | 17.53 | 0.032 | 0.81 | 0.468 | 11.89 | 500       |
| RW500062A | 1/2        | 1.125 | 28.58 | 0.690 | 17.53 | 0.062 | 1.57 | 0.468 | 11.89 | 500       |
| RW875062A | 7/8        | 1.343 | 34.11 | 0.940 | 23.88 | 0.062 | 1.57 | 0.825 | 20.96 | 500       |

RWM Series  
Metric Retaining Washers



## Specifications:

- Material: Nylon
- Color: Natural

## Features:

- Designed to grip outside of screw shank
- Easily slides on to the screw but is retained by the screw once assembled
- Ideal for applications requiring pre-assembly of the screw and washer
- Reduces assembly time and cost
- Ideal for outdoor environments
- Resistant to corrosion, oil, abrasion and most chemicals

| Item No. | Screw Size | D (OD) | d (ID) | H (Thickness) | Pack Qty. |
|----------|------------|--------|--------|---------------|-----------|
|          |            | mm     | mm     | mm            |           |
| RWM050A  | M2         | 5.00   | 2.70   | 1.50          | 1,000     |
| RWM100A  | M3         | 5.50   | 3.20   | 2.20          | 1,000     |
| RWM150A  | M3         | 9.00   | 3.20   | 1.50          | 1,000     |
| RWM200A  | M4         | 7.00   | 4.30   | 2.30          | 1,000     |
| RWM250A  | M4         | 12.00  | 4.30   | 1.40          | 1,000     |
| RWM300A  | M5         | 8.50   | 5.30   | 2.80          | 1,000     |
| RWM350A  | M5         | 11.50  | 5.30   | 1.40          | 1,000     |
| RWM400A  | M6         | 10.00  | 6.40   | 2.80          | 1,000     |
| RWM450A  | M6         | 18.00  | 6.40   | 2.00          | 500       |
| RWM500A  | M8         | 13.00  | 8.40   | 2.80          | 500       |
| RWM550A  | M10        | 21.00  | 10.50  | 2.50          | 500       |

015XXXXXX03  
Retaining PE Flat Washer

## Specifications:

- Material: Polyethylene

## Features:

- Designed to grip outside of screw shank
- Easily slides on to the screw but is retained by the screw once assembled
- Ideal for applications requiring pre-assembly of the screw and washer
- Reduces assembly time and cost

| Item No.      | Color | Ø"d" I.D.   | Ø"D" O.D.  | "H"        | Fits Screw | Pack Qty. |
|---------------|-------|-------------|------------|------------|------------|-----------|
| 015002500503  | Red   | .106 (2.7)  | .256 (6.5) | .043 (1.1) | #3 (M2.5)  | 1,000     |
| 015003000503  | Red   | .126 (3.2)  | .276 (7)   | .055 (1.4) | #5 (M3)    | 1,000     |
| 015004000503  | Red   | .169 (4.3)  | .354 (9)   | .043 (1.1) | #8 (M4)    | 1,000     |
| 015005000503  | Red   | .209 (5.3)  | .433 (11)  | .051 (1.3) | #10 (M5)   | 1,000     |
| 015006000503  | Red   | .252 (6.4)  | .472 (12)  | .063 (1.6) | 1/4 (M6)   | 500       |
| 015008000503  | Red   | .331 (8.4)  | .669 (17)  | .079 (2)   | 5/16 (M7)  | 500       |
| 015102500203  | Grey  | .106 (2.7)  | .197 (5)   | .059 (1.5) | #3 (M2.5)  | 1,000     |
| 015103000203  | Grey  | .126 (3.2)  | .217 (5.5) | .083 (2.1) | #5 (M3)    | 1,000     |
| 015104000203  | Grey  | .169 (4.3)  | .276 (7)   | .087 (2.2) | #8 (M4)    | 1,000     |
| 015105000203  | Grey  | .209 (5.3)  | .335 (8.5) | .106 (2.7) | #10 (M5)   | 1,000     |
| 015106000203  | Grey  | .252 (6.4)  | .394 (10)  | .106 (2.7) | 1/4 (M6)   | 1,000     |
| 015108000203  | Grey  | .331 (8.4)  | .512 (13)  | .106 (2.7) | 5/16 (M7)  | 500       |
| 015202508703  | Blue  | .106 (2.7)  | .197 (5)   | .039 (1)   | #3 (M2.5)  | 1,000     |
| 015203008703  | Blue  | .126 (3.2)  | .236 (6)   | .039 (1)   | #5 (M3)    | 1,000     |
| 015204008703  | Blue  | .169 (4.3)  | .315 (8)   | .039 (1)   | #8 (M4)    | 1,000     |
| 015205008703  | Blue  | .209 (5.3)  | .394 (10)  | .039 (1)   | #10 (M5)   | 1,000     |
| 015206008703  | Blue  | .252 (6.4)  | .433 (11)  | .059 (1.5) | 1/4 (M6)   | 1,000     |
| 015208008703  | Blue  | .331 (8.4)  | .591 (15)  | .059 (1.5) | 5/16 (M7)  | 500       |
| 01521,0008703 | Blue  | .413 (10.5) | .709 (18)  | .059 (1.5) | 3/8 (M10)  | 500       |