



## RSM



plug-in socket modules for IDEC RH1B and Eagle Signal 1601C relays



"H" dimension 5mm less on TS 35 x 7.5 rail

## RSM/RSRM

plug-in socket modules for IDEC RH2B DPDT relays




"H" dimension 5mm less on TS 35 x 7.5 rail

| Type           | Channels | Coil Voltage | T            | Cat. No.      | Cat. No.      | Type           | Channels | Coil Voltage | T            | Cat. No.      | Cat. No.      |
|----------------|----------|--------------|--------------|---------------|---------------|----------------|----------|--------------|--------------|---------------|---------------|
| without relays |          |              |              | DC*           | AC            | without relays |          |              |              | DC*           | AC            |
| RSM 1/6        | 1        | 6V           | 20mm(0.79in) | <b>910516</b> | <b>910458</b> | RSM 1/12       | 1        | 12V          | 45mm(1.75in) | <b>911331</b> | <b>911351</b> |
| RSM 1/12       | 1        | 12V          | 20mm(0.79in) | <b>910525</b> | <b>910459</b> | RSM 1/24       | 1        | 24V          | 45mm(1.75in) | <b>911341</b> | <b>911361</b> |
| RSM 1/24       | 1        | 24V          | 20mm(0.79in) | <b>910443</b> | <b>910503</b> | RSM 1/20       | 1        | 120V         | 45mm(1.75in) |               | <b>911371</b> |
| RSM 1/48       | 1        | 48V          | 20mm(0.79in) | <b>910526</b> |               |                |          |              |              |               |               |
| RSM 1/110      | 1        | 110V         | 20mm(0.79in) | <b>910529</b> | <b>910455</b> |                |          |              |              |               |               |
| RSM 1/220      | 1        | 220V         | 20mm(0.79in) |               | <b>910504</b> |                |          |              |              |               |               |


## OS1

socket modules for plug-in I/O modules



OS 1/2

OS 1/4





"H" dimension 5mm less on TS 35 x 7.5 rail

\* Height shown to top of socket—add I/O module for overall height.

| Type                                        | Channels | H            | W            | T             | Cat. No.      |
|---------------------------------------------|----------|--------------|--------------|---------------|---------------|
| Each channel wired separately; rail-mounted |          |              |              |               |               |
| OS 1/1                                      | 1        | 55mm(2.16in) | 87mm(3.43in) | 35mm(1.38in)  | <b>911413</b> |
| OS 1/2                                      | 2        | 55mm(2.16in) | 87mm(3.43in) | 71mm(2.80in)  | <b>911426</b> |
| OS 1/4                                      | 4        | 55mm(2.16in) | 87mm(3.43in) | 130mm(5.12in) | <b>911414</b> |

## RS 21 and RS 23



plug-in relay socket modules  
for 8- and 11-pin octal relays



"H" dimension 5mm less on TS 35 x 75 rail  
\* Height shown to top of socket—add relay for overall height

## RS

plug-in relay socket modules  
for miscellaneous relays



"H" dimension 5mm less on TS 35 x 75 rail  
\* Height shown to top of socket—add relay for overall height

| Type                                                                                                                                                | Matching Relays | Contact Rating | H and T        | Cat. No.<br>DC* | Cat. No.<br>AC | Type                                                  | Matching Relays      | Contact Rating | H and T        | Cat. No.<br>DC* | Cat. No.<br>AC |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|----------------|----------------|-----------------|----------------|-------------------------------------------------------|----------------------|----------------|----------------|-----------------|----------------|
| RS 21A                                                                                                                                              | DPDT            | 250V, 10A      | H 44mm(1.73in) | <b>910003</b>   | <b>910350</b>  | RS 3A                                                 | DPDT                 | 250V, 5A       | H 42mm(1.63in) | <b>910101</b>   | <b>910350</b>  |
|                                                                                                                                                     | 8-pin octal     |                | T 40mm(1.57in) |                 |                |                                                       | P&B KH Series        |                | T 35mm(1.38in) |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Midtex 156           |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Aromat HC2           |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                | RS 6A                                                 | DPDT                 | 250V, 5A       | H 40mm(1.57in) | <b>910107</b>   | <b>910100</b>  |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | P&B R10 Series       |                | T 35mm(1.38in) |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Aromat K2 Series     |                |                |                 |                |
| RS 23 A                                                                                                                                             | 3 PDT           | 250V, 10A      | H 44mm(1.73in) | <b>913500</b>   | <b>913501</b>  | RS KU2                                                | 3 PDT                | 250V, 5A       | H 39mm(1.52in) | <b>910519</b>   | <b>910521</b>  |
|                                                                                                                                                     | 11-pin octal    |                | T 40mm(1.57in) |                 |                |                                                       | P&B KU Series        |                | T 45mm(1.77in) |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Magnecraft 388CP     |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | IDEC RR 1 2&3B       |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Aromat HP Series     |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                | RS 14A                                                | 4 PDT                | 250V, 5A       | H 42mm(1.63in) | <b>910083</b>   | <b>910090</b>  |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | P&B KH Series        |                | T 45mm(1.77in) |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Midtex 156, IDEC RY4 |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Aromat HC2           |                |                |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                | RS 18A                                                | 4 PDT                | 250V, 5A       | H 40mm(1.57in) | <b>910522</b>   | <b>910523</b>  |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | P&B R10 Series       |                | T 45mm(1.77in) |                 |                |
|                                                                                                                                                     |                 |                |                |                 |                |                                                       | Aromat K4 Series     |                |                |                 |                |
| Mounting (  TS 35 rail <b>30340</b> / End bracket <b>30350</b> ) |                 |                |                |                 |                | * DC versions have suppression diodes across the coil |                      |                |                |                 |                |
| Mounting (  TS 32 rail <b>12200</b> / End bracket <b>20010</b> ) |                 |                |                |                 |                |                                                       |                      |                |                |                 |                |