


Shape

KPEG753





Rated Frequency (Hz)	3,600±500
Operating Voltage Range (V.D.C.)	6~28
Current Consumption (mA)	Max.10@12VDC
Sound Pressure Level (dB)	Min.82dB@30cm / 12VDC
Rated Voltage	12
Tone	Slow Pulse (3.0Hz±20%)@ 12VDC
Operating Temperature (°C)	-30 ~ +85
Storage Temperature (°C)	-40 ~ +95
Weight (Gram)	18.5
Material	ABS UL-94 1/16" HB (Gray)

Dimension



Top View



Tol : ±0.5 Unit : mm

Characteristic / Schematic Diagram