

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0210200051](#)
Status: **Active - Custom**
Overview:
Description: 0.50mm (.020") Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 6 Circuits, 0.03m (1.18") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
Series [21020](#)
Comments Contacts on the same side, Type A
Geographic Area Americas
Overview Premo-Flex®#153;
Product Name Premo-Flex™FFC Jumper

Physical

Cable Length 0.03m (1.18")
Circuits (Loaded) 6
Packaging Type Bag
Pitch - Term. Interface (in) 0.020 In
Pitch - Term. Interface (mm) 0.50 mm
Temperature Range - Operating -40°C to +80°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum 0.5A
Voltage - Maximum 30V


Solder Process Data

Duration at Max. Process Temperature (seconds) 250
Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 250

Material Info

Reference - Drawing Numbers

Sales Drawing SD-21020-001



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[21020 Series](#)

Use With

Any 0.50mm (.020") Pitch Molex FFC/FPC
connector