

Type 360410

Single terminal block, solderable, horizontal wire entry, open construction, double solder pins, screw brought down by hand

Technical Data



A / AWG 15 / 30 - 18

Insulation co-ordination according to IEC 664-1

Protection category according to IEC 529

IP00

Tightening torque UL 4.4 lb-in max.

Solder pin dimension 2 x 1.0 mm

Recommended pc board hole dia.

Ø 1.5 mm

Solder pin length 3.5 mm

Type 360322

Single terminal block, solderable, horizontal wire entry, wire protector, open construction, double solder pins, screw brought down by hand

Technical Data



A / AWG 15 / 30 - 16



A / AWG 15 / 30 - 16

Insulation co-ordination according to IEC 664-1

Protection category according to IEC 529

IP00

Tightening torque UL 6 lb-in max.

Solder pin dimension 2 x 1.0 mm


Recommended pc board hole dia.

Ø 1.5 mm

Solder pin length 3.5 mm


Dimensions in mm

1 mm = 0.0394 in.



Dimensions in mm

1 mm = 0.0394 in.



Part numbers (P/N)

Type 360410

P/N 360410

Part numbers (P/N)

Type 360322

P/N 360322