






- THIS PLUG WILL MATE WITH ANY 24C7, SIZE 5 RECEPTACLE IN AMPLIMITE SERIES.
- MAXIMUM WIRE INSULATION TO BE USED WITH THIS PLUG IS .068 DIA.
- STAINLESS STEEL RETENTION ARE INCLUDED IN INSERT SSSEMBLY.
- THIS CONNECTOR ACCEPTS SIZE 20 PIN SIGNAL CONTACTS. NOT SUPPLIED WITH CONNECTOR.
- INSERTION/EXTRACTION TOOL USED FOR SIZE 20 PIN SIGNAL CONTACTS IS 91067-2.
- USE 7 POWER OR COAX PIN CONTACTS. CONSULT PRODUCT ENGR. FOR MORE DETAILS.

~~UL/CSA DESIGNATION STAMPED IN THIS AREA.~~

446631-1
PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MANJUNATH G M 27-May-15	TE Connectivity	
		CHK CHARLES THOMAS 27-May-15		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD CHARLES THOMAS 27-May-15	NAME	PLUG ASS'Y, AMPLIMITE COAX MIX, 24C7, SIZE 5, SERIES 109, BLINDMATE
	0 PLC ± -	PRODUCT SPEC	SIZE	CAGE CODE
	1 PLC ± -	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT	A100779	446631
CUSTOMER DRAWING		SCALE	4:1	SHEET 1 OF 1 REV D