




Features:

- UL Approved
- High Quality Open Style Toroidal Transformer
- Dual Primary/Secondary windings
- Thermal fuses fitted to each Primary winding
- Very low level radiated magnetic field
- Supplied with mounting Kit
- 100% electrical and flash tested.
- Compliant Standards, EN61558, EN60950, UL, C-UL and CE



Lead Length: 150mm stripped and tinned ends

VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (A)	Regulation (Typ. %)	Temp Rise (°C)	Height x Dia. (mm)	Weight (Kg)
15	VTX-146-015-206	115 / 230	2 x 6	1.25	16	26	33 x 65	0.33
15	VTX-146-015-209	115 / 230	2 x 9	0.83	16	26	33 x 65	0.33
15	VTX-146-015-212	115 / 230	2 x 12	0.63	16	26	33 x 65	0.33
15	VTX-146-015-215	115 / 230	2 x 15	0.5	16	26	33 x 65	0.33
15	VTX-146-015-218	115 / 230	2 x 18	0.42	16	26	33 x 65	0.33
15	VTX-146-015-224	115 / 230	2 x 24	0.3125	16	26	33 x 65	0.33
15	VTX-146-015-225	115 / 230	2 x 25	0.3	16	26	33 x 65	0.33
30	VTX-146-030-206	115 / 230	2 x 6	2.5	14	40	33 x 74	0.45
30	VTX-146-030-209	115 / 230	2 x 9	1.67	14	40	33 x 74	0.45
30	VTX-146-030-212	115 / 230	2 x 12	1.25	14	40	33 x 74	0.45
30	VTX-146-030-215	115 / 230	2 x 15	1	14	40	33 x 74	0.45
30	VTX-146-030-218	115 / 230	2 x 18	0.83	14	40	33 x 74	0.45
30	VTX-146-030-224	115 / 230	2 x 24	0.625	14	40	33 x 74	0.45
30	VTX-146-030-225	115 / 230	2 x 25	0.6	14	40	33 x 74	0.45
50	VTX-146-050-206	115 / 230	2 x 6	4.17	14	42	33 x 82	0.6
50	VTX-146-050-209	115 / 230	2 x 9	2.78	14	42	33 x 82	0.6
50	VTX-146-050-212	115 / 230	2 x 12	2.08	14	42	33 x 82	0.6
50	VTX-146-050-215	115 / 230	2 x 15	1.67	14	42	33 x 82	0.6
50	VTX-146-050-218	115 / 230	2 x 18	1.39	14	42	33 x 82	0.6
50	VTX-146-050-224	115 / 230	2 x 24	1.05	14	42	33 x 82	0.6
50	VTX-146-050-225	115 / 230	2 x 25	1	14	42	33 x 82	0.6
50	VTX-146-050-255	115 / 230	2 x 55	0.45	14	42	33 x 82	0.6

Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements
The information contained in this document is subject to change without notice.

VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (A)	Regulation (Typ. %)	Temp Rise (°C)	Height x Dia. (mm)	Weight (Kg)
60	VTX-146-060-206	115 / 230	2 x 6	5	15	50	34 x 85	0.8
60	VTX-146-060-209	115 / 230	2 x 9	3.33	15	50	34 x 85	0.8
60	VTX-146-060-212	115 / 230	2 x 12	2.5	15	50	34 x 85	0.8
60	VTX-146-060-215	115 / 230	2 x 15	2	15	50	34 x 85	0.8
60	VTX-146-060-218	115 / 230	2 x 18	1.66	15	50	34 x 85	0.8
60	VTX-146-060-224	115 / 230	2 x 24	1.25	15	50	34 x 85	0.8
60	VTX-146-060-225	115 / 230	2 x 25	1.2	15	50	34 x 85	0.8
60	VTX-146-060-230	115 / 230	2 x 30	1	15	50	34 x 85	0.8
60	VTX-146-060-250	115 / 230	2 x 55	0.55	15	50	34 x 85	0.8
80	VTX-146-080-209	115 / 230	2 x 9	4.44	11	50	40 x 90	1
80	VTX-146-080-212	115 / 230	2 x 12	3.33	11	50	40 x 90	1
80	VTX-146-080-215	115 / 230	2 x 15	2.67	11	50	40 x 90	1
80	VTX-146-080-218	115 / 230	2 x 18	2.22	11	50	40 x 90	1
80	VTX-146-080-224	115 / 230	2 X 24	1.66	11	50	40 x 90	1
80	VTX-146-080-225	115 / 230	2 X 25	1.6	11	50	40 x 90	1
80	VTX-146-080-230	115 / 230	2 X 30	1.33	11	50	40 x 90	1
80	VTX-146-080-255	115 / 230	2 X 55	0.73	11	50	40 x 90	1
100	VTX-146-100-209	115 / 230	2 x 9	5.55	11	53	45 x 91	1.2
100	VTX-146-100-212	115 / 230	2 x 12	4.15	11	53	45 x 91	1.2
100	VTX-146-100-215	115 / 230	2 x 15	3.33	11	53	45 x 91	1.2
100	VTX-146-100-218	115 / 230	2 x 18	2.77	11	53	45 x 91	1.2
100	VTX-146-100-224	115 / 230	2 x 24	2.08	11	53	45 x 91	1.2
100	VTX-146-100-225	115 / 230	2 x 25	2	11	53	45 x 91	1.2
100	VTX-146-100-230	115 / 230	2 x 30	1.66	11	53	45 x 91	1.2
120	VTX-146-120-212	115 / 230	2 x 12	5	10	55	45 X 98	1.32
120	VTX-146-120-215	115 / 230	2 x 15	4	10	55	45 X 98	1.32
120	VTX-146-120-218	115 / 230	2 x 18	3.33	10	55	45 X 98	1.32
120	VTX-146-120-224	115 / 230	2 x 24	2.5	10	55	45 X 98	1.32
120	VTX-146-120-225	115 / 230	2 x 25	2.4	10	55	45 X 98	1.32
120	VTX-146-120-230	115 / 230	2 x 30	2	10	55	45 X 98	1.32
120	VTX-146-120-255	115 / 230	2 x 55	1.09	10	55	45 X 98	1.32
160	VTX-146-160-209	115 / 230	2 x 9	8.88	8	55	47 X 105	1.6
160	VTX-146-160-212	115 / 230	2 x 12	6.67	8	55	47 X 105	1.6
160	VTX-146-160-215	115 / 230	2 x 15	5.33	8	55	47 X 105	1.6
160	VTX-146-160-218	115 / 230	2 x 18	4.44	8	55	47 X 105	1.6
160	VTX-146-160-224	115 / 230	2 x 24	3.33	8	55	47 X 105	1.6
160	VTX-146-160-225	115 / 230	2 x 25	3.2	8	55	47 X 105	1.6
160	VTX-146-160-230	115 / 230	2 x 30	2.67	8	55	47 X 105	1.6
160	VTX-146-160-255	115 / 230	2 x 55	1.45	8	55	47 X 105	1.6

VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (A)	Regulation (Typ. %)	Temp Rise (°C)	Height x Dia. (mm)	Weight (Kg)
225	VTX-146-225-212	115 / 230	2 x 12	9.38	7	60	51 X 110	2.2
225	VTX-146-225-215	115 / 230	2 x 15	7.5	7	60	51 X 110	2.2
225	VTX-146-225-218	115 / 230	2 x 18	6.3	7	60	51 X 110	2.2
225	VTX-146-225-224	115 / 230	2 x 24	4.68	7	60	51 X 110	2.2
225	VTX-146-225-225	115 / 230	2 x 25	4.5	7	60	51 X 110	2.2
225	VTX-146-225-230	115 / 230	2 x 30	3.75	7	60	51 X 110	2.2
225	VTX-146-225-250	115 / 230	2 x 50	2.25	7	60	51 X 110	2.2
225	VTX-146-225-255	115 / 230	2 x 55	2.05	7	60	51 X 110	2.2
250	VTX-146-250-212	115 / 230	2 x 12	10.42	7	60	50 X 119	2.5
250	VTX-146-250-215	115 / 230	2 x 15	8.33	7	60	50 X 119	2.5
250	VTX-146-250-218	115 / 230	2 x 18	6.95	7	60	50 X 119	2.5
250	VTX-146-250-225	115 / 230	2 x 25	5	7	60	50 X 119	2.5
250	VTX-146-250-230	115 / 230	2 x 30	4.16	7	60	50 X 119	2.5
250	VTX-146-250-235	115 / 230	2 x 35	3.57	7	60	50 X 119	2.5
250	VTX-146-250-240	115 / 230	2 x 40	3.125	7	60	50 X 119	2.5
250	VTX-146-250-245	115 / 230	2 x 45	2.77	7	60	50 X 119	2.5
250	VTX-146-250-250	115 / 230	2 x 50	2.5	7	60	50 X 119	2.5
250	VTX-146-250-255	115 / 230	2 x 55	2.27	7	60	50 X 119	2.5
300	VTX-146-300-212	115 / 230	2 x 12	12.5	6	60	55 X 125	3.0
300	VTX-146-300-215	115 / 230	2 x 15	10	6	60	55 X 125	3.0
300	VTX-146-300-218	115 / 230	2 x 18	8.33	6	60	55 X 125	3.0
300	VTX-146-300-225	115 / 230	2 x 25	6	6	60	55 X 125	3.0
300	VTX-146-300-230	115 / 230	2 x 30	5	6	60	55 X 125	3.0
300	VTX-146-300-235	115 / 230	2 x 35	4.28	6	60	55 X 125	3.0
300	VTX-146-300-255	115 / 230	2 X 55	2.73	6	60	55 X 125	3.0
500	VTX-146-500-225	115 / 230	2 x 25	10	6	68	61 X 138	4.3
500	VTX-146-500-230	115 / 230	2 x 30	8.33	6	68	61 X 138	4.3
500	VTX-146-500-235	115 / 230	2 x 35	7.14	6	68	61 X 138	4.3
500	VTX-146-500-240	115 / 230	2 x 40	6.25	6	68	61 X 138	4.3
500	VTX-146-500-245	115 / 230	2 x 45	5.56	6	68	61 X 138	4.3
500	VTX-146-500-250	115 / 230	2 x 50	5	6	68	61 X 138	4.3
500	VTX-146-500-255	115 / 230	2 x 55	4.55	6	68	61 X 138	4.3
625	VTX-146-625-225	115 / 230	2 x 25	12.5	5	70	72 X 144	5.2
625	VTX-146-625-240	115 / 230	2 x 40	7.8	5	70	72 X 144	5.2
625	VTX-146-625-245	115 / 230	2 X 45	6.95	5	70	72 X 144	5.2
625	VTX-146-625-250	115 / 230	2 x 50	6.25	5	70	72 X 144	5.2
625	VTX-146-625-255	115 / 230	2 x 55	5.68	5	70	72 X 144	5.2
800	VTX-146-800-240	115 / 230	2 x 40	10	5	72	65 X 163	6.3
800	VTX-146-800-245	115 / 230	2 x 45	8.88	5	72	65 X 163	6.3
800	VTX-146-800-250	115 / 230	2 x 50	8	5	72	65 X 163	6.3
800	VTX-146-800-255	115 / 230	2 x 55	7.27	5	72	65 X 163	6.3
1000	VTX-146-1000-240	115 / 230	2 x 40	12.5	4	75	71 X 167	7.48
1000	VTX-146-1000-245	115 / 230	2 x 45	11.11	4	75	71 X 167	7.48
1000	VTX-146-1000-250	115 / 230	2 x 50	10	4	75	71 X 167	7.48
1000	VTX-146-1000-255	115 / 230	2 x 55	9.09	4	75	71X 167	7.48

The information contained in this document is subject to change without notice.