



FEATURES:

- ✓ Ideal for resistant measurements below 1 ohm.
- ✓ Compatible with Fluke and Keithley 4 wire test instruments.
- ✓ Four wire measurement using the Kelvin Clip reduces the IR drop in test leads that can cause measurement inaccuracies on 5 1/2 and 6 1/2 digit DMM's
- ✓ Additional banana plug and alligator clip are connected to the shield of the coaxial cables for added shield protection.
- ✓ Clamps and banana plugs are color coded for ease of testing.

MATERIALS:

Banana plugs: Gold plated Beryllium Copper for low contact resistance.



RATINGS:

Operating Voltage:

Hands free usage in controlled voltage environments: 45 Vrms maximum. For CE compliance: not intended for hand-held use at voltages above 33 Vrms/45 Vdc.

Current: 5 Amps

Operating Temperature: +122° F (+50° C)

ORDERING INFORMATION: Model 5940

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com