



DMM,1KV AC/DC(DM-200A)(CALIB)

Digital Multimeter

Cat No: DM-200A-C

UPC No: 783310357568

Description

- Measures Voltage, Current, Resistance And Frequency
- Tests Continuity And Diodes
- Backlit LCD With 6,000 Count Display
- Two Voltage Detection Modes - Non-Contact Or Using A Single Test Lead
- Beepjack Warns When Test Leads Are Incorrectly Inserted In Current Measurement Terminals
- Automatic And Manual Range Selection
- Relative Offset Mode To See Changes In Measurements
- Data Hold
- Use Optional USB / RS-232 Interface DMSC-2U For Direct-To-PC Logging
- Lifetime Limited Warranty
- Includes Certificate of Calibration

Specifications

- Amperage Measurement : 600, 6000 MICAMP, 60, 600 MILAMP, 6, 8 AMP
- Battery : (2) 1.5 V AAA
- Capacitance : 60, 600 NFD, 6, 60, 600, 3000MFD
- Display : Backlit LCD With 6,000 Count
- Frequency Measurement : 10 HZ - 50 KHZ Sine Wave, 5 HZ - 999.9 KHZ Logic Level Square Wave
- Includes : (2) 1.5V AAA Batteries, Bead Temperature Probe (DM-210A, DM-510A Only, 400 DEG F/204 DEG C max), Test leads, ProtectiveBoot
- Measurement Category : CAT IV 300 V, CAT III 600 V, CAT II 1000 V
- Replacement Part : TSG-3 Sure-Grip Test Leads
- Resistance Measurement : 600 OHM, 6, 60, 600 KOHM, 6, 60 MOHM
- Standard : CAT IV, CAT III, CAT II, C/ULUS Listed, CE Listed
- Sub Brand : ESM
- Temperature Rating : K Type, -58 To 1832 DEG F (-50 To 1000 DEG C)
- Type : Digital
- Voltage Measurement : 60, 600 MILV, 6, 60, 600, 1000 V