







SPECIFICATIONS:

1. CURRENT CARRYING CAPACITY:

1) AC: 100V 1A MAX.

2) DC: 12V 2A MAX.

2. CONTACT RESISTANCE: 30mΩ MAX.

3. INSULATION RESISTANCE: 50MΩ MIN. AT DC 250V

4. VOLTAGE WITHSTAND: AC 250V 1 MINUTE.

5. INSERTION FORCE: 1KG-5KG


6. WITHDRAWAL FORCE: 1KG-4KG

7. LIFE TEST: 5,000 CYCLES MIN AFTER TESTING CONTACT RESISTANCE SHALL NOT EXCEED 100 mΩ.

8. NICKEL PLATED THICKNESS: 1μm (1μm) MIN.

SILVER PLATED THICKNESS: 0.6 μm (24μm) MIN.

10. UNLESS OTHERWISE SPECIFIED TOLERANCE ARE: ±0.1mm



3

4

5

6

7

8

今入企業有限公司
JIN RUH CO., LTD.

JR 2730