


AA-CD-301-02

- STUD SIZES: ($\alpha=0.05$)

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$



WIRE SIZE: 22-18 AWG
25-1.5 MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	*ID" MIN.			AVAILABLE STUD SIZES	STOCK THICKNESS	
AA-333-	.273 <u>6.93</u>	.240 <u>6.10</u>	.591 <u>15.01</u>	.062 <u>1.57</u>			04, 06, 08, 10	.028 ^{+ .001} _{- .001} <u>.71</u>	
AA-3111-	.187 <u>4.75</u>	.173 <u>4.39</u>	.490 <u>12.45</u>	.054 <u>1.37</u>			02, 04	.031 ^{+ .001} _{- .001} <u>.79</u>	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED	REFERENCE		SCALE:	NTS	DATE	TITLE:			
FRACTION	DEC.	ANG.		DRWN. BY:	JJ	11-27-84	RING TONGUE TERMINAL VERSAKRIMP 300-SERIES		
±	±	±		CHKD. BY:	GZ	11-30-84			
				APPRD. BY:					
								DWG. NO.	A CUSTOMER DWG.

ETC
INCORPORATED
cmolex

DWG. NO.	A	CUSTOMER DWG.
-------------	---	------------------