

	1	2	3	4	5	6	7									
A	Pin 7 Pin 1 300MM±10MM Pin 7 Pin 1 SATA Pin 7 Pin 1 P1 Pin Assignment P1 P2 1 2 3 4 5 6 7 1 2 3 4 5 6 7 Drain Wire White *2C Draing Wire/2C White *2C Drain Wire Material: • Cable: UL2725 [26AWG(1/0.404)*2+D(1/0.32)*2+AL]*2F - OD 2.2*7.8MM - Jacket Red (200C/RD-16#) • P1 & P2 Connectors: Serial ATA 7-pin/Female Crimp Type - Pin G/F - Insulator Black • Jacket: PVC 45P, Black Electrical: • 100% Open, Short, MisWire Test • Conduct Resistance: 2Ω Max. • Insulation Resistance: 5MΩ Min. • Dielectric test: 300V DC Unit: MM±0.25MM Scale 1:1 TOLERANCE X.X ±0.40 X.XX ±0.25 X.XXX ±0.15 Angle ±3° RoHS Complaint Modification Date Name ASSMANN components Item No. AK-SATA-030DL-R Title Serial ATA (SATA)/Angled Connection Cable - 0.3 Meter Drawing No. rev00 Replace Sheet <tr><td></td><td>1</td><td>2</td><td>3</td><td>4</td><td>5</td><td>6</td><td>7</td><td></td></tr>								1	2	3	4	5	6	7	
	1	2	3	4	5	6	7									