



Copyright FCI.

Product number
10080068-XXXXXXXXLF

PART NUMBER DESCRIPTION:
10080068 - X X X XXXX LF

LF: LEAD FREE (NOTE 10)

CUSTOMER SPECIFIC DASH NUMBER

STYLE:

	END P1 CONNECTOR STYLE	END P2
1:	STRAIGHT	WITH WIRE TERMINATION
2:	STRAIGHT	NO TERMINATION BLUNT CUT/WIRES ONLY
3:	R/A	WITH WIRE TERMINATION
4:	R/A	NO TERMINATION BLUNT CUT/WIRES ONLY

CODING KEY:

	ORIENTATION
A:	0°
B:	90°
C:	180°
D:	270°
E:	CUSTOMER INSTALLED

CABLE DESCRIPTION

	WIRE SIZE	DESCRIPTION	NOTES	STYLE
E:	2x6mm ²	STRANDED	HALOGEN FREE	STRAIGHT
F:	10mm ²	STRANDED	HALOGEN FREE	R/A
G:	16mm ²	STRANDED	HALOGEN FREE	STRAIGHT, R/A
H:	25mm ²	STRANDED	HALOGEN FREE	R/A

CUSTOMER SPECIFIC
CABLE ASSEMBLY

rev	ecn no	dr	date
A	V08-0434	DAI	2008-10-09
B	V09-0194	SM	2009-04-24

www.fciconnect.com			surface ☒		tolerance std		projection 		 MM	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	D. INGRAM	2008-07-28	ANGULAR	LINEAR	0.X	±0.X	size	A4	Scale	7:100
Eng	C. GROSS	2008-07-28			0.XX	±0.10				
Chr	C. GROSS	2008-07-28			0.XXX	±0.XXX				
Appr	C. GROSS	2008-07-28	0° ±2°				ECN		V09-0194	
			Product family			C&A		Spec ref		
		title	PWR TWINBLADE I/O SINGLE ENDED				10080068		Rev B	
			CABLE ASSEMBLY PART NUMBER SCHEME							
		catalog no	-				CUSTOMER		sheet 1 of 2	



Product number
10080068-XXXLXXXLF

PART NUMBER DESCRIPTION:
10080068 - X X X LXXX LF

LF: LEAD FREE (NOTE 10)

STYLE:

	END P1 CONNECTOR STYLE	END P2
1:	STRAIGHT	WITH WIRE TERMINATION
2:	STRAIGHT	NO TERMINATION BLUNT CUT/WIRES ONLY
3:	R/A	WITH WIRE TERMINATION
4:	R/A	NO TERMINATION BLUNT CUT/WIRES ONLY

LENGTH IN CENTIMETERS
EXAMPLE OF LXXX:
L090 = 90cm
L150 = 150cm

CODING KEY:

	ORIENTATION
A:	0°
B:	90°
C:	180°
D:	270°
E:	CUSTOMER INSTALLED

CABLE DESCRIPTION

	WIRE SIZE	DESCRIPTION	NOTES	STYLE
E:	2x6mm ²	STRANDED	HALOGEN FREE	STRAIGHT
F:	10mm ²	STRANDED	HALOGEN FREE	R/A
G:	16mm ²	STRANDED	HALOGEN FREE	STRAIGHT, R/A
H:	25mm ²	STRANDED	HALOGEN FREE	R/A

GENERAL PRODUCT OFFERING
FCI WEBSITE