





1. FOR USE WITH AMP PRO-CRIMPER II HAND TOOL, PART # 354940-1, OR WITH THE 626 SERIES PNEUMATIC TOOL WITH ADAPTER #679304-1
2. REQUIRES PRO-CRIMPER II DIE SET PART # 58436-1. FOR CONTACT AND BRAID TERMINATION.
3. REQUIRES PRO-CRIMPER II DIE SET PART # 58485-1. FOR CONTACT AND BRAID TERMINATION.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED STRIP LENGTHS

3, 4	OBSOLETE	RG-9/U & 214/U	CONTACT: .100, BRAID: .429	DETAIL D	9-221132-5	415247-4	415256-2	5415255-4
		RG-58/AU & 58C/U	CONTACT: .068, BRAID: .213	DETAIL C	9-221132-0	415246-4	415256-1	5415255-1
		CABLE	HEX CRIMP HEIGHTS IN INCHES	STRIP LENGTH	3 FERRULE QTY=1	2 CONTACT QTY=1	1 PLUG ASSY QTY=1	PART NUMBER