




HONEYWELL PART NUMBER
V15T16-CZ100A05-K
PRODUCT CODE
CFW2044

REV	DOCUMENT	CHANGED BY	CHECK
A	0038670	VS 10APR08	BLR



- NOTES:
- TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM		DRAWN	KSR	01APR08	Honeywell									
		CONTACT ARRANGEMENT S.P.D.T		TOLERANCES UNLESS NOTED:		CHECK	RJ	01APR08						TITLE SWITCH - BASIC				
OPERATING FORCE: 120gf MAX. DIFFERENTIAL FORCE: RELEASE FORCE: 20gf MIN. FREE POSITION: OPERATING POSITION: 20.6±0.8MM. PRE-TRAVEL: 1.6MM MAX. DIFFERENTIAL TRAVEL: 0.4MM MAX. OVER-TRAVEL: 0.8MM MIN. FULL OVERTRAVEL FORCE:						THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY										
		 16(4)A 250V~ 25T125 μ 5E4  16A 1/2HP 125/250VAC		NO PLACE X ± ± ONE PLACE .X ± ± TWO PLACE .XX ± ± 0.40 THREE PLACE .XXX ± ± ANGLES X ± ± 2°		THIRD ANGLE PROJECTION 		AutoCAD		SCALE	NTS			SHEET	1	OF 1		