

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120005031](#)
Status: **Active**
Overview: [PC Network Interface Cards](#)
Description: Direct-Link PCU-ETHIO Card, PROFINET IO-Controller/ IO-Device, 1 Channel, PCI 3.3/ 5V - OPC/DLL/LIB/DAS - Control

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Network Interface
Series	112000
Application	IO Control
Approvals	CE certified
Communication Speed	Ethernet: 10/100 Mbps
Mounting Style	PC Slot
Operating System	Windows7, Windows8/8.1, Windows Server 2003, Windows Server 2008, Windows Server 2012, Windows Vista, WindowsXP
Overview	PC Network Interface Cards
Product Literature Order No	987650-6906
Product Name	applicom IO
Protocol	PROFINET
Protocol Detail	PROFINET IO-Controller, PROFINET IO-Device
Slot	Universal PCI 3.3V/5V
Software Downloads	DRL-EPN-PCU
Type	Ethernet Card
UPC	883906507206
Woodhead	Yes

Physical

Channels	1
Interface	DLL, OPC DA
Net Weight	140.000/g
Network Connection Type	Ethernet: RJ45
Packaging Type	Carton
Processor	AMD SC520
Temperature Range - Operating	0°C to +65°C

Electrical


Current - Maximum Input	5.5W
EMC	EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2
Supply Voltage	3.3/5V

Material Info

Engineering Number	DRL-EPN-PCU
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	SD-112000-5031-001
---------------	--------------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[112000 Series](#)