




## Heyco-Flex™ Quick Twist Conduit Fittings

For use with Heyco-Flex™ II Tubing  
**Straight-Thru, Snap-In Hubs**

- One-piece solution with smooth internal surfaces provides for easier wire routing, protection, and installation.
- Unique locking fingers accommodate various panel thicknesses.
- Snap-in Fittings are UL recognized for use with Heyco-Flex II tubing. See page 2-3.
- Easy, permanent assembly: the installer twists the tubing over the connector ferrule.
- All nylon construction is resistant to salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL certification and testing.)
- Suitable for a wide array of electrical applications:
  - Commercial and Industrial HVAC Systems
  - Motorized Equipment
  - Enclosed Power Sources
  - Garage Door Openers
  - Major Appliances
- Finishing collars available to neaten rough cut tubing ends.
- **New! Assembly Tool** available for assembling Quick Twist Fittings into HF1 and HF2 Conduit and Tubing. See page 2-12.

FITS TUBING TRADE SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS								
	Black	Gray		A Mounting Hole Dia.		B Overall Length		C Body Length		D Wrenching Nut Thk.		E Flat Size
1/4	8515	8516	HFC 1/4-S-twist	.540	13,7	1.330	33,8	.344	8,7	.090	2,3	.750 19,0
3/8	8485	8486	HFC 3/8-S-twist	.875	22,2	1.376	35,0	.391	9,9	.090	2,3	1.000 25,4
1/2	8490	8491	HFC 1/2-S-twist									
3/4	8495	8496	HFC 3/4-S-twist	1.093	27,8	1.495	38,0	.391	9,9	.090	2,3	1.250 31,8

Standard colors black and gray. Consult Heyco for other colors.



## Heyco-Flex™ Quick Twist Finishing Collars



For use with Heyco-Flex™ I and II Quick Twist Conduit Fittings

FITS CONDUIT/ TRADE SIZE	PART NO.		DESCRIPTION
	Black	Gray	
3/8	8474	8482	HFC TWIST 3/8 COLLAR
1/2	8475	8483	HFC TWIST 1/2 COLLAR
3/4	8476	8484	HFC TWIST 3/4 COLLAR

Standard colors black and gray. Consult Heyco for other colors.  
 (Not available in 1/4").

*Quick  
Specs*

Material	Nylon 6/6
Certifications	Recognized under the Component Program of Underwriters' Laboratories File E121095
Flammability Rating	94V-2
Material Temperature Index	Maximum temperature on part not to exceed 221°F (105°C)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[0055](#) [0056](#)