


REV. 1 10/10/95

**COIL:**

RESISTANCE	7500 OHMS ± 10%
NOMINAL VOLTAGE	115.0 VAC (60-400 Hz)
MUST OPERATE	66.0 VAC (60-400 Hz)
MUST RELEASE	7.0 VAC (60-400 Hz)

**CUSTOMER DATA SHEET**



**ENVIRONMENT:**

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

**CONTACT RATING:** 10 AMPS 30 VDC RES.  
10 AMPS 115 VAC 400 Hz, 6A 30 VDC  
INDUCTIVE 100,000 OPERATIONS

**NOTES:** OPERATE TIME 15 MS MAX.  
RELEASE TIME 20 MS MAX.  
CONTACT BOUNCE 5 MS MAX. (NC)  
2 MS MAX. (NO)

DR. R.B. 5/17/93 CK. 10/10/95

**COMMUNICATIONS INSTRUMENTS, INC.**

CUST. HI-G  
CUST. NO. 2TR-1B-215

TYPE '07' RELAY

B07B942BZ1-8020