

DESCRIPTION: M8 FEMALE - CABLE MOUNT - SOLDER CUP - 4 POS.

NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK
CONTACT: PHOSPHOR BRONZE
SHELL: BRASS
NUT: BRASS
O-RING: NBR, BLACK

FINISH:


CONTACT: GOLD PLATED
OVER 50µ" NICKEL
GROUND: BRIGHT TIN 60µ"
SHELL: NICKEL PLATED

ELECTRICAL


RATED CURRENT: 5A
RATED VOLTAGE: 125V
INSULATION RESISTANCE: 100 MΩhms MIN.
CONTACT RESISTANCE: 10 MΩhms MAX.
WATER PROOF: IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C
WIRE GAUGE: 24-28 AWG






NUT



854-004-203RLSY

1 = GOLD FLASH
4 = 10µ" GOLD



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

CHECKED:

DATE:

NorComp

SCALE:

N.T.S.

SHEET

OF

1 1

REV

1

DWG NO.

854-004-203RLSY