


| REV. | DATE | DESCRIPTION |
|------|----------|-----------------|
| NC | 04/14/04 | INITIAL RELEASE |



Amphenol Connex

CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .324”
 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068”

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE
IN MILLIMETERS. DIMENSIONS IN [] ARE IN
INCHES AND FOR CUSTOMER REFERENCE ONLY.

| UNLESS OTHERWISE SPECIFIED, DIMENSIONS IN [] ARE IN MILLIMETERS, DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. | | | | | | | | | |
|--------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|--|--|--|------------------------------------------|--|--|--|------|
| UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm \pm 0.20mm 8 - 30mm \pm 0.40mm 30 - 120mm \pm 0.50mm | | | | | | | | | |
| UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE: .020 - .315 = \pm 0.007" .315 - 1.180 = \pm 0.015" 1.180 - 4.724 = \pm 0.020" | | | | | | | | | |
| 8 | DRAWN | | | | APPROVALS | | | | DATE |
| 7 | G.R.S. | | | | 04/14/04 | | | | |
| 6 | CHECKED | | | | PART DESCRIPTION | | | | |
| 5 | ISSUED | | | | F CRIMP PLUG (FOR BELDEN 1695A CABLE) | | | | |
| 4 | SHEET 1 OF 1 | | | | REV. NC | | | | |
| 3 | PART NO. 222171 | | | | SIZE A | | | | |
| 2 | MATERIAL | | | | SCALE N/A | | | | |
| 1 | DESCRIPTION | | | | REV. NC | | | | |
| | FINISH | | | | SIZE A | | | | |
| | QTY | | | | SCALE N/A | | | | |
| | DO NOT SCALE DRAWING | | | | REV. NC | | | | |
| | CAD FILE C:/222/222171.DWG | | | | SIZE A | | | | |
| | DWG. NO. 222171.DWG | | | | SCALE N/A | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[222171](#)