

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0357607110](#)
Status: **Contact Molex**
Overview: [splice](#)
Description: Wire Splice, 16-20 AWG, Post-Tin Plating

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-35760-001 \(PDF\)](#)
[Product Specification PS-35760-003 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E134962


General
Product Family Splices
Series [35760](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [splice](#)
Product Name N/A

Physical
Barrel Type Open
Insulation None
Material - Metal Brass
Packaging Type Reel
Temperature Range - Operating -30°C to +105°C
Wire Insulation Diameter 3.5mm (.138")
Wire Size AWG 16, 18, 20
Wire Size mm² 0.50 - 1.50

Electrical
Voltage - Maximum 200V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-35760-001
Product Specification PS-35760-003
Sales Drawing SD-35760-002



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35760Series](#)