



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		A	REVISED PER ECO-13-001939	08NOV2013	KH	MB

MATERIAL:
HOUSING: POLYAMIDE 6, UL94V-2.
COLOR: OFF WHITE.
CONTACT: BRASS, TIN PLATED.
WIRE PROTECTOR: STAINLESS STEEL.
SCREW: M5, STEEL, W/ ZINC PLATED NON-
HEXAVALENT CHROMATE (CHROME III).

ELECTRICAL:
MAX CURRENT: 65A (UR) 70A (CSA)
OPERATING VOLTAGE: 600V PER UL FILE E60677
WIRE RANGE: 6-14 UL AND 6-22 AWG FOR (CSA)
DIELECTRIC WITHSTAND: 6000V.

ENVIRONMENT:
CONTINUOUS WORKING TEMP.: -35°C TO 100°C.

145	170.7	12	TSB200012	1-1776312-2
130.5	156.2	11	TSB200011	1-1776312-1
116	141.7	10	TSB200010	1-1776312-0
101.5	127.2	9	TSB200009	1776312-9
87	112.7	8	TSB200008	1776312-8
72.5	98.2	7	TSB200007	1776312-7
58	83.7	6	TSB200006	1776312-6
43.5	69.2	5	TSB200005	1776312-5
29	54.7	4	TSB200004	1776312-4
14.5	40.2	3	TSB200003	1776312-3
—	25.7	2	TSB200002	1776312-2
—	11.2	1	TSB200001	1776312-1
DIM B	DIM A	NO OF POS	CATALOG NUMBER	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± 0.3

2 PLC ± 0.25

3 PLC ± —

4 PLC ± —

ANGLES ± 2°

FINISH —

DWN
S SCHLEGEL
3/22/05

CHK
C RICHARD
3/22/05

APVD
C RICHARD
3/22/05

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

EUROPA TERMINAL BLOCK, 14.5MM PITCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1776312

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
A

TE Connectivity