

DM Duplex Receptacle

DESCRIPTIONS

Packaged in a touch-proof enclosure to eliminate the possibility of accidental shock. The universal mounting foot allows the outlet box to be mounted either vertically or horizontally in your panel. Touch-proof screw terminal block provides a reliable connection.

FEATURES

- DIN-rail mount duplex receptacle
- Vertical or horizontal mounting
- Snap on foot provides fast installation or can be fixed with screws in control cabinet
- Fits on 35 mm wide DIN-rail
- Ground prong reversed for greater protection
- Screw terminal connection via touch-proof terminal blocks
- Available with GFI (Ground Fault Interrupting)
- UR Recognized

APPLICATIONS

- Test & Diagnostic Equipment
- Computers/Printers
- Power Tools
- Soldering Iron
- Displays
- Lighting
- Fan



GENERAL SPECIFICATIONS

Technical Data

Rated Voltage..... 120 V AC
 Rated Current..... 15 AMPS
 Maximum Wire Size #10 AWG

Housing Data

Color Black
 Material..... PVC V01550
 Maximum Temperature 40°C

Dimensions

Length..... 5.32 in. (135 mm)
 Width..... 2.95 in. (75 mm)
 Depth 2.56 in. (65 mm)

DM Duplex Receptacle Selection Chart

AMP	CATALOG NUMBER	APPROX. SHIP WEIGHT LBS (Kg)
15	DRR15	.41 (.19)
15	DRR15GFI	.46 (.21)