







REV.	DATE	DESCRIPTION
A	03/17/03	MODIFY BODY LENGTH
B	07/31/07	REVISE PART ORIENTATION



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	G.R.S.								07/31/07
7	HEX NUT	BRASS	GOLD	1		CHECKED			PART DESCRIPTION SMA R/A BULKHEAD P.C. MOUNT JACK						
6	LOCK WASHER	BRASS	GOLD	1		ISSUED									
5	CONTACT PIN	BRASS	GOLD	1		SHEET	1 OF 1		PART NO. 132203–12						
4	INSULATOR	TEFLON	NATURAL	1											
3	CONTACT PIN	BER. COPPER	GOLD	1					DWG. NO. 132203–12.DWG						
2	INSULATOR	TEFLON	NATURAL	1				REV. B							
1	HOUSING/BODY	BRASS	GOLD	1											
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/132/132203–12.DWG									