




LOC	DIST	REVISIONS					
HM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E1	REVISED PER ECO-11-005027	14MAR2011	RK	HMR
			F	REV PER ECO-12-012918	16JUL2012	JM	JB



1. MATERIAL: HOUSING - 94V-0 RATED POLYCARBONATE CLEAR TERMINAL - 0.36 [0.014] THICK PHOSPHAR BRONZE PLATED WITH 1.27 μ m [0.00050] MINIMUM THICK GOLD IN LOCALIZED AREA, OVER 2.54 μ m [0.000100] MINIMUM THICK NICKEL UNDERPLATE.
WIRE HOLDER - POLYCARBONATE MAKROLON CLEAR.
SHIELD - BRASS DIN 17660 - CuZn33
2. DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
3. PLUG WILL ACCEPT A 24-26 AWG STRANDED CONDUCTOR, PROVIDED THE INSULATION CONDUCTOR DIAMETER IS WITHIN .89 - 1.09 [0.035 - .043]; WITH THE SUM OF DIAMETERS FOR ALL EIGHT CONDUCTORS WITHIN THE CABLE MUST NOT EXCEED 7.8MM [0.31 IN]. CABLE JACKET DIAMETER OF 5.0 -6.0MM [0.20-.24 IN].
4. TERMINATED DIMENSION 6.15 [0.242] MAXIMUM.
5. PACKAGE 1,000 ASSEMBLIES, 1,000 WIRE HOLDERS, AND 1,000 SHIELDS.
6. PACKAGE 100 ASSEMBLIES, 100 WIRE HOLDERS, AND 100 SHIELDS.
7. PACKAGE 25 ASSEMBLIES, 25 WIRE HOLDERS, AND 25 SHIELDS.
8. PACKAGE 500 ASSEMBLIES, 500 WIRE HOLDERS, AND 500 SHIELDS.
9. MODULAR PLUG BOOT, PART NUMBER 737893-X (X-DENOTES VARIOUS COLORS), MAY BE USED WITH KIT ASSEMBLY SHOWN.
10. UL RECOGNIZED: FILE NUMBER E81956.



7	5-1375202-4
6	5-1375202-3
8	5-1375202-2
5	5-1375202-1
PACKAGE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL	30JUL01	 TE Connectivity		
DIMENSIONS: MM[INCHES]		CHK M. DELPHIAS	06AUG01			NAME
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. DELPHIAS	06AUG01	KIT, 8 POSN,MOD PLUG, STRANDED WIRE, CAT 6		
 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES FINISH		PRODUCT SPEC		RESTRICTED TO		
		108-1990				
		APPLICATION SPEC				
		114-13035				
MATERIAL		WEIGHT		SIZE	CAGE CODE	DRAWING NO
- 		-		A1	00779	C1375202
CUSTOMER DRAWING		SCALE		8:1	SHEET	1 OF 1