




1. 208492-1 MATES WITH AMP RECEPTACLE 208493-1.
2. THIS PLUG ACCEPTS TWENTY EIGHT (28) TYPE 20 DM OR TYPE 20 DF SOCKET CONTACTS. MAXIMUM WIRE INSULATION DIAMETER = .068.
3. AMP PART NUMBER AND DATE CODE TO BE LOCATED ON COUPLING RING.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC * - 3 PLC DEC * - ANGLES * -		DR 7-2-92 H. MOLL.		208492-1 PART NO	
SEE CALLOUT		CHK 12-29-92 R. STONE		AMP Incorporated Harleburg, PA 17105-3808	
SEE CALLOUT		APPD 12-29-92 K. BEAVER		NAME	
SEE CALLOUT		APPD 12-29-92 C. RONDE		PLUG ASSEMBLY, REVERSE SEX, SERIES 2, 22-28, CMC	
FINISH		PRODUCT SPEC 108-10040		SIZE	
SEE CALLOUT		APPLICATION SPEC		CASE CODE 00779	
WEIGHT		SCALE 2:1		DRAWING NO 208492	
				SHEET 1 OF 1	

CUSTOMER DRAWING