


D


C

B


A



SECTION B-B/TOPVIEW



FRONT VIEW




BOTTOM VIEW

OBSOLETE

OBSOLETE

PART NUMBER	'N' POS. PER ROW	DIMENSIONS	
		A	B
216602-2	2	5.08	2.54
216602-3	3	7.62	5.08
216602-4	4	10.16	7.62
216602-5	5	12.70	10.16
216602-6	6	15.24	12.70
216602-7	7	17.78	15.24
216602-8	8	20.32	17.78
1-216602-0	10	25.40	22.86
1-216602-2	12	30.48	27.94
OBSOLETE 1-216602-3	13	33.02	30.48
1-216602-4	14	35.56	33.02
1-216602-6	16	40.64	38.10
2-216602-0	20	50.80	48.26
OBSOLETE 2-216602-3	23	58.42	55.88
OBSOLETE 2-216602-4	24	60.96	58.42
OBSOLETE 2-216602-6	26	66.04	63.50
OBSOLETE 2-216602-9	29	73.66	71.12
OBSOLETE 3-216602-1	31	78.74	76.20
3-216602-6	36	91.44	88.90
3-216602-8	38	96.52	93.98
5-216602-0	50	127.00	124.46
5-216602-1	51	129.54	127.00




SECTION A-A

⌀ 0.35 M A B C


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IR	—		H6	PART STATUS UPDATED IN PART LIST TABLE	30MAY2014	KJK	JK

NOTES:

- 1 TO DETERMINE DIMENSION TAKE N= NR. OF POS
FOR EXAMPLE, 10 POS., $N \times 2.54 = 25.4\text{mm}$.
FOR ORDER NR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE, 2 POS.= 216602-2 (SHORTEST VERSION)
65 POS.= 6-216602-5 (LONGEST VERSION)
- 2 HOUSING MATERIAL, GREEN GLASS FILLED POLYESTER, UL 94V-0
CONTACT MATERIAL, PHOSPHOR BRONZE.
- 3 PLATING, UNDER COATING, 1.3μm Ni
AT CONTACT PLACE, 0.8μm Au
AT SOLDER-TINES, 3.0-5.0μm TIN
- 4 MATES WITH 0.63 SQUARE/ROUND MODU POSTS
- 5 CONTACT POINT
- 6 RECOMMENDED P.C.BOARD THICKNESS 1.6mm
- 7 PRINTED: THE WORD "TE" [FOR 2 TO 6 POS]
THE WORD "TE" & PRODUCTION DATE [FOR 7 TO 12 POS]
THE WORD "TE", PRODUCTION DATE & BASIC PART NO. [FOR 13 TO 65 POS]
AND A DASHED LINE OVER THE LENGTH OF HOUSING TO
INDICATE CONTACT MATING SIDE.



REAR VIEW



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	19/12/91	TE Connectivity			
		CHK	19/12/91				
		APVD	19/12/91	NAME			
		PRODUCT SPEC		HV 190 HOR. ASSY SINGLE ROW, GOLD VERSION, MAX. 65 POSITION			
		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	—	A2	00779	C=216602	—
		CUSTOMER DRAWING		SCALE	10:1	SHEET	1 OF 1
						REV	H6

D

C

216602

B

A