







LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECR-12-013103	21MAR2013	K.M	E.T








- △ HOUSING: PPA RESIN, BLACK.
CONTACTS: PHOSPHOR BRONZE.
RETENTION LEG: BRASS.
- 2. CONNECTOR WILL ACCOMMODATE PRINTED CIRCUIT BOARD THICKNESS OF 0.79 TO 1.60 [.031 TO .063].
- △ CONNECTOR WILL ACCOMMODATE MATING PRINTED CIRCUIT BOARD OF 1.60±0.08 [.063±.003] THICKNESS.
- △ SEE TABLE. G, J, AND H INDICATE NUMBER OF POSITIONS MARKED ON ASSEMBLY.
- △ CONTACTS: GOLD FLASH OVER
0.76µm [.000030] MIN PALLADIUM-NICKEL PLATING ON CONTACT AREA,
3.81µm [.000150] MIN MATTE TIN PLATING ON SOLDER TAILS,
1.27µm [.000050] MIN NICKEL UNDERPLATING OVERALL.
- △ RETENTION LEG: 3.81µm [.000150] MIN MATTE TIN OVER 1.27µm [.000050] MIN NICKEL.
- 7 WAVE SOLDER CAPABLE TO 265°C PER TE SPEC 109-202, CONDITION B.
- △ ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.



B1	OBSOLETE	130	66	65	93.90 [3.697]	91.26 [3.593]	86.82 [3.418]	△△	130	3-1734331-3
		80	41		62.22 [2.450]	59.51 [2.343]	55.07 [2.168]	△△	80	2-1734331-1
		68	35		54.57 [2.148]	51.89 [2.043]	47.45 [1.868]	△△	68	1-1734331-7
B1	OBSOLETE	50	26	25	43.10 [1.697]	40.46 [1.593]	36.02 [1.418]	△△	50	1734331-9
		J △	H △	G △	C	B	A	FINISH	POSTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 06JUN2006	 TE Connectivity					
		CHK S. HOU 06JUN2006						
DIMENSIONS: mm		APVD W.J. KE 06JUN2006	NAME					
		PRODUCT SPEC 108-57876	RECEPTACLE ASSEMBLY, V/T, BOARD-TO-BOARD, .050 SERIES I, CHAMP*					
		APPLICATION SPEC						
MATERIAL SEE NOTE		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C=1734331	RESTRICTED TO —		
FINISH SEE NOTE		CUSTOMER DRAWING				SCALE —	SHEET 1 OF 3	REV B1

LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



VERTICAL RECEPTACLE ASSEMBLY MATED TO VERTICAL PLUG STRADDLE ASSEMBLY

VERTICAL RECEPTACLE ASSEMBLY MATED TO RIGHT ANGLE PLUG ASSEMBLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
		CHK				
DIMENSIONS: mm		APVD	NAME			
		PRODUCT SPEC	RECEPTACLE ASSEMBLY, V/T, BOARD-TO-BOARD, .050 SERIES I, CHAMP*			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		CUSTOMER DRAWING	A3	00779	C=1734331	
			SCALE	SHEET	REV	
				2 OF 3	B1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, — .

© COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC


DW

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			


STOPPER



TUBE



CARTON



⑥ OBSOLETE

4.74

6.13

5.01

5.79

G.W./CARTON (KG)

3.55

4.65

3.52

4.15

N.W./CARTON (KG)

54

54

54

54

PCS/TUBE

8

16

16

24

TUBES/CARTON

432

864

864

1296

QUANTITY/CARTON (PCS)

3-1734331-3

2-1734331-1

1-1734331-7

1734331-9

PART NUMBER

130

80


68

50

POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

RECEPTACLE ASSEMBLY, V/T,
BOARD-TO-BOARD, .050 SERIES I, CHAMP*

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734331

SCALE

SHEET 3 OF 3

REV B1

1470-19 (1/08)