



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MAXIMUM CABLE DIAMETER	PANEL DIMENSIONS		WEIGHT LBS./100 PCS. (g)
		THICKNESS	HOLE SIZE	
SICH25	.25 (6.4)	.03/.10 (0.8/2.5)	.250 (6.4)	.11 (50)

NOTE:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

(DIMENSIONS IN PARENTHESES ARE METRIC)									
CAD FILENAME/LAYERS GB0239JK_PB_SICH25_00									
PANDUIT CORP. TINLEY PARK, ILLINOIS									
SNAP-IN CLIP SICH25									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± N/A (.XXX) ± .010 (.25) (.XX) ± .02 (.5) ANGLES ± N/A									
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.									
DRAWN BY LGG MAT'L: SCALE 2/1									
DATE 9-4-02 NYLON 6/6 DRAWING NO. GB0239JK DWG SIZE A									
CHK'D									
R	9-4-02	LGG		INITIAL RELEASE.	GB0239JK	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP